

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Specialty Mirrors](#)

Hot Mirrors



- Ideal for Reducing Heat
- Reflects >90% of the NIR and IR
- Transmits >85% of Visible Light

Common Specifications

Optical Properties

Substrate: BOROFLOAT®	Surface Quality: 80-50
Surface Flatness (P-V): 4 - 6λ	Coating Type: Dielectric

Technical Information

Products

AOI (°)	Dia. (mm)	Dimensions (mm)	Thickness (mm)	Stock Number	Price	Buy
0.00	25.00	-	3.30	#43-842	A\$78.69 Volume Pricing	20+ In Stock
0.00	-	25.0 x 25.0	3.30	#43-843	A\$78.69 Volume Pricing	20+ In Stock
0.00	-	101.6 x 127.0	3.30	#43-453	A\$309.82 Volume Pricing	16 In Stock
0.00	50.00	-	3.30	#54-515	A\$103.82 Volume Pricing	11 In Stock
0.00	-	50.0 x 50.0	3.30	#43-452	A\$93.94 Volume Pricing	20+ In Stock
45.00	25.00	-	3.30	#43-955	A\$78.69 Volume Pricing	20+ In Stock
45.00	-	12.5 x 12.5	1.10	#62-624	A\$65.51 Volume Pricing	20+ In Stock
0.00	-	20.0 x 20.0	1.10	#62-627	A\$72.51 Volume Pricing	8 In Stock
0.00	12.50	-	1.10	#62-621	A\$65.51 Volume Pricing	20+ In Stock
45.00	12.50	-	1.10	#62-622	A\$65.51 Volume Pricing	20+ In Stock
0.00	-	12.5 x 12.5	1.10	#62-623	A\$65.51 Volume Pricing	20+ In Stock
45.00	-	25.0 x 25.0	3.30	#43-956	A\$78.69 Volume Pricing	15 In Stock
0.00	20.00	-	1.10	#62-625	A\$72.51 Volume Pricing	20+ In Stock
45.00	-	101.6 x 127.0	3.30	#43-958	A\$309.82 Volume Pricing	20+ In Stock
45.00	20.00	-	1.10	#62-626	A\$72.51 Volume Pricing	20+ In Stock
45.00	50.00	-	3.30	#55-233	A\$103.82 Volume Pricing	14 In Stock
45.00	-	50.0 x 50.0	3.30	#43-957	A\$93.94 Volume Pricing	20+ In Stock

45.00	-	20.0 x 20.0	1.10	#62-628	A\$72.51 Volume Pricing	13 In Stock
0.00	-	35.0 x 35.0	3.30	#62-629	A\$89.82 Volume Pricing	2 In Stock
45.00	-	35.0 x 35.0	3.30	#62-630	A\$89.82 Volume Pricing	20+ In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com