

[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [Visible Windows](#)

TECHSPEC® $\lambda/4$ N-BK7 Precision Windows



- Circular and Rectangular Sizes from 2mm to 200mm
- 8 Broadband Anti-Reflection Coating Options Available
- World's Largest Selection of Standard N-BK7 Windows
- Also Available with [Ultra-Thin N-BK7 Windows](#)

Common Specifications

Physical & Mechanical Properties

Bevel:	Protective as needed	Clear Aperture (%):	90
Edges:	Fine Ground	Knoop Hardness (kg/mm²):	610.00
Parallelism (arcmin):	<1	Poisson's Ratio:	0.21
Young's Modulus (GPa):	82		

Optical Properties

Abbe Number (v_d):	64.17		
Index of Refraction (n_d):	1.516	Surface Quality:	60-40

Material Properties

Density (g/cm³):	2.51
------------------------------------	------

Technical Information

Products

Dia. (mm)	Dimensions (mm)	Thickness (mm)	Coating	Stock Number	Price	Buy
2.00	-	1.00	Uncoated	#27-674	A\$66.74 Volume Pricing	20+ In Stock
2.50	-	1.00	Uncoated	#27-675	A\$71.28 Volume Pricing	4 In Stock
3.00	-	1.00	Uncoated	#27-719	A\$75.81 Volume Pricing	9 In Stock
4.00	-	1.00	Uncoated	#27-815	A\$84.87 Volume Pricing	20+ In Stock
5.00	-	1.00	Uncoated	#20-464	A\$98.88 Volume Pricing	20+ In Stock
5.00	-	1.00	MgF ₂ (400-700nm)	#23-355	A\$118.66 Volume Pricing	Contact Us
5.00	-	1.00	VIS-EXT (350-700nm)	#23-443	A\$143.38 Volume Pricing	1 In Stock
5.00	-	1.00	VIS-NIR (400-1000nm)	#23-399	A\$143.38 Volume Pricing	1 In Stock
5.00	-	1.00	VIS 0° (425-675nm)	#23-377	A\$137.61 Volume Pricing	5 In Stock
5.00	-	1.00	YAG-BBAR (500-1100nm)	#23-465	A\$143.38 Volume Pricing	11 In Stock
5.00	-	1.00	NIR I (600-1050nm)	#23-421	A\$137.61 Volume Pricing	2 In Stock
5.00	-	1.00	NIR II (750-1550nm)	#25-783	A\$137.61 Volume Pricing	5 In Stock
5.00	-	2.00	Uncoated	#45-573	A\$98.88 Volume Pricing	20+ In Stock
5.00	-	2.00	MgF ₂ (400-700nm)	#45-574	A\$118.66 Volume Pricing	20+ In Stock
5.00	-	2.00	VIS-EXT (350-700nm)	#13-286	A\$143.38 Volume Pricing	10 In Stock

5.00	-	2.00	VIS-NIR (400-1000nm)	#48-448	A\$143.38 Volume Pricing	9 In Stock
5.00	-	2.00	VIS 0° (425-675nm)	#47-515	A\$137.61 Volume Pricing	9 In Stock
5.00	-	2.00	YAG-BBAR (500-1100nm)	#13-308	A\$143.38 Volume Pricing	16 In Stock
5.00	-	2.00	NIR I (600-1050nm)	#83-464	A\$137.61 Volume Pricing	2 In Stock
5.00	-	2.00	NIR II (750-1550nm)	#25-784	A\$137.61 Volume Pricing	20+ In Stock
-	6.00 x 6.00	2.00	Uncoated	#29-300	A\$98.88 Volume Pricing	17 In Stock
9.00	-	1.00	Uncoated	#20-472	A\$98.88 Volume Pricing	12 In Stock
9.00	-	1.00	MgF ₂ (400-700nm)	#23-356	A\$118.66 Volume Pricing	1 In Stock
9.00	-	1.00	VIS-EXT (350-700nm)	#23-444	A\$143.38 Volume Pricing	5 In Stock
9.00	-	1.00	VIS-NIR (400-1000nm)	#23-400	A\$143.38 Volume Pricing	Contact Us
9.00	-	1.00	VIS 0° (425-675nm)	#23-378	A\$137.61 Volume Pricing	1 In Stock
9.00	-	1.00	YAG-BBAR (500-1100nm)	#23-466	A\$143.38 Volume Pricing	5 In Stock
9.00	-	1.00	NIR I (600-1050nm)	#23-422	A\$137.61 Volume Pricing	20+ In Stock
9.00	-	1.00	NIR II (750-1550nm)	#25-785	A\$137.61 Volume Pricing	5 In Stock
9.00	-	2.00	Uncoated	#49-121	A\$98.88 Volume Pricing	20+ In Stock
9.00	-	2.00	MgF ₂ (400-700nm)	#49-122	A\$118.66 Volume Pricing	20+ In Stock
9.00	-	2.00	VIS-EXT (350-700nm)	#13-287	A\$143.38 Volume Pricing	5 In Stock

9.00	-	2.00	VIS-NIR (400-1000nm)	#49-124	A\$143.38 Volume Pricing	20+ In Stock
9.00	-	2.00	VIS 0° (425-675nm)	#49-123	A\$137.61 Volume Pricing	20+ In Stock
9.00	-	2.00	YAG-BBAR (500-1100nm)	#13-309	A\$143.38 Volume Pricing	8 In Stock
9.00	-	2.00	NIR I (600-1050nm)	#83-465	A\$137.61 Volume Pricing	7 In Stock
9.00	-	2.00	NIR II (750-1550nm)	#25-786	A\$137.61 Volume Pricing	4 In Stock
10.00	-	1.00	Uncoated	#20-480	A\$98.88 Volume Pricing	20+ In Stock
10.00	-	1.00	MgF ₂ (400-700nm)	#23-357	A\$118.66 Volume Pricing	7 In Stock
10.00	-	1.00	VIS-EXT (350-700nm)	#23-445	A\$143.38 Volume Pricing	6 In Stock
10.00	-	1.00	VIS-NIR (400-1000nm)	#23-401	A\$143.38 Volume Pricing	3 In Stock
10.00	-	1.00	VIS 0° (425-675nm)	#23-379	A\$137.61 Volume Pricing	3 In Stock
10.00	-	1.00	YAG-BBAR (500-1100nm)	#23-467	A\$143.38 Volume Pricing	7 In Stock
10.00	-	1.00	NIR I (600-1050nm)	#23-423	A\$137.61 Volume Pricing	2 In Stock
10.00	-	1.00	NIR II (750-1550nm)	#25-787	A\$137.61 Volume Pricing	20+ In Stock
-	10.00 x 10.00	1.00	Uncoated	#20-539	A\$98.88 Volume Pricing	16 In Stock
-	10.00 x 10.00	1.00	MgF ₂ (400-700nm)	#23-369	A\$118.66 Volume Pricing	Contact Us
-	10.00 x 10.00	1.00	VIS-EXT (350-700nm)	#23-457	A\$143.38 Volume Pricing	Contact Us
-	10.00 x 10.00	1.00	VIS-NIR (400-1000nm)	#23-413	A\$143.38 Volume Pricing	1 In Stock

-	10.00 x 10.00	1.00	VIS 0° (425-675nm)	#23-391	A\$137.61 Volume Pricing	Contact Us
-	10.00 x 10.00	1.00	YAG-BBAR (500-1100nm)	#23-479	A\$143.38 Volume Pricing	Contact Us
-	10.00 x 10.00	1.00	NIR I (600-1050nm)	#23-435	A\$137.61 Volume Pricing	1 In Stock
-	10.00 x 10.00	1.00	NIR II (750-1550nm)	#25-788	A\$137.61 Volume Pricing	3 In Stock
10.00	-	2.00	Uncoated	#45-074	A\$98.88 Volume Pricing	20+ In Stock
10.00	-	2.00	MgF ₂ (400-700nm)	#45-256	A\$118.66 Volume Pricing	20+ In Stock
10.00	-	2.00	VIS-EXT (350-700nm)	#13-288	A\$143.38 Volume Pricing	8 In Stock
10.00	-	2.00	VIS-NIR (400-1000nm)	#45-657	A\$143.38 Volume Pricing	20+ In Stock
10.00	-	2.00	VIS 0° (425-675nm)	#47-516	A\$137.61 Volume Pricing	Contact Us
10.00	-	2.00	YAG-BBAR (500-1100nm)	#13-310	A\$143.38 Volume Pricing	6 In Stock
10.00	-	2.00	NIR I (600-1050nm)	#83-466	A\$137.61 Volume Pricing	15 In Stock
10.00	-	2.00	NIR II (750-1550nm)	#25-789	A\$137.61 Volume Pricing	5 In Stock
-	10.00 x 10.00	2.00	Uncoated	#49-620	A\$98.88 Volume Pricing	20+ In Stock
-	10.00 x 10.00	2.00	MgF ₂ (400-700nm)	#49-623	A\$118.66 Volume Pricing	20+ In Stock
-	10.00 x 10.00	2.00	VIS-EXT (350-700nm)	#13-289	A\$143.38 Volume Pricing	8 In Stock
-	10.00 x 10.00	2.00	VIS-NIR (400-1000nm)	#49-631	A\$143.38 Volume Pricing	6 In Stock
-	10.00 x 10.00	2.00	VIS 0° (425-675nm)	#49-627	A\$137.61 Volume Pricing	5 In Stock

-	10.00 x 10.00	2.00	YAG-BBAR (500-1100nm)	#13-311	A\$143.38 Volume Pricing	5 In Stock
-	10.00 x 10.00	2.00	NIR I (600-1050nm)	#83-467	A\$137.61 Volume Pricing	1 In Stock
-	10.00 x 10.00	2.00	NIR II (750-1550nm)	#25-790	A\$137.61 Volume Pricing	4 In Stock
12.50	-	1.00	Uncoated	#20-491	A\$98.88 Volume Pricing	20+ In Stock
12.50	-	1.00	MgF ₂ (400-700nm)	#23-358	A\$118.66 Volume Pricing	Contact Us
12.50	-	1.00	VIS-EXT (350-700nm)	#23-446	A\$143.38 Volume Pricing	6 In Stock
12.50	-	1.00	VIS-NIR (400-1000nm)	#23-402	A\$143.38 Volume Pricing	20+ In Stock
12.50	-	1.00	VIS 0° (425-675nm)	#23-380	A\$137.61 Volume Pricing	3 In Stock
12.50	-	1.00	YAG-BBAR (500-1100nm)	#23-468	A\$143.38 Volume Pricing	1 In Stock
12.50	-	1.00	NIR I (600-1050nm)	#23-424	A\$137.61 Volume Pricing	4 In Stock
12.50	-	1.00	NIR II (750-1550nm)	#25-791	A\$137.61 Volume Pricing	5 In Stock
12.50	-	1.00	BBAR (1650-3000nm)	#70-280	A\$160.68 Volume Pricing	4 In Stock
12.50	-	2.00	Uncoated	#20-495	A\$98.88 Volume Pricing	20+ In Stock
12.50	-	2.00	MgF ₂ (400-700nm)	#23-359	A\$118.66 Volume Pricing	Contact Us
12.50	-	2.00	VIS-EXT (350-700nm)	#23-447	A\$143.38 Volume Pricing	2 In Stock
12.50	-	2.00	VIS-NIR (400-1000nm)	#23-403	A\$143.38 Volume Pricing	5 In Stock
12.50	-	2.00	VIS 0° (425-675nm)	#23-381	A\$137.61 Volume Pricing	2 In Stock

12.50	-	2.00	YAG-BBAR (500-1100nm)	#23-469	A\$143.38 Volume Pricing	5 In Stock
12.50	-	2.00	NIR I (600-1050nm)	#23-425	A\$137.61 Volume Pricing	1 In Stock
12.50	-	2.00	NIR II (750-1550nm)	#25-792	A\$137.61 Volume Pricing	5 In Stock
12.50	-	3.00	Uncoated	#45-075	A\$98.88 Volume Pricing	20+ In Stock
12.50	-	3.00	MgF ₂ (400-700nm)	#45-257	A\$118.66 Volume Pricing	Contact Us
12.50	-	3.00	VIS-EXT (350-700nm)	#13-290	A\$143.38 Volume Pricing	7 In Stock
12.50	-	3.00	VIS-NIR (400-1000nm)	#45-658	A\$143.38 Volume Pricing	3 In Stock
12.50	-	3.00	VIS 0° (425-675nm)	#47-517	A\$137.61 Volume Pricing	20+ In Stock
12.50	-	3.00	YAG-BBAR (500-1100nm)	#13-312	A\$143.38 Volume Pricing	11 In Stock
12.50	-	3.00	NIR I (600-1050nm)	#83-468	A\$137.61 Volume Pricing	14 In Stock
12.50	-	3.00	NIR II (750-1550nm)	#25-793	A\$137.61 Volume Pricing	11 In Stock
-	12.50 x 12.50	3.00	Uncoated	#49-621	A\$98.88 Volume Pricing	20+ In Stock
-	12.50 x 12.50	3.00	MgF ₂ (400-700nm)	#49-624	A\$118.66 Volume Pricing	20+ In Stock
-	12.50 x 12.50	3.00	VIS-EXT (350-700nm)	#13-291	A\$143.38 Volume Pricing	7 In Stock
-	12.50 x 12.50	3.00	VIS-NIR (400-1000nm)	#49-632	A\$143.38 Volume Pricing	5 In Stock
-	12.50 x 12.50	3.00	VIS 0° (425-675nm)	#49-628	A\$137.61 Volume Pricing	2 In Stock
-	12.50 x 12.50	3.00	YAG-BBAR (500-1100nm)	#13-313	A\$143.38 Volume Pricing	4 In Stock

-	12.50 x 12.50	3.00	NIR I (600-1050nm)	#83-469	A\$137.61 Volume Pricing	5 In Stock
-	12.50 x 12.50	3.00	NIR II (750-1550nm)	#25-794	A\$137.61 Volume Pricing	2 In Stock
12.70	-	3.00	Uncoated	#15-423	A\$98.88 Volume Pricing	20+ In Stock
12.70	-	3.00	MgF ₂ (400-700nm)	#15-427	A\$118.66 Volume Pricing	5 In Stock
12.70	-	3.00	VIS-EXT (350-700nm)	#15-787	A\$143.38 Volume Pricing	Contact Us
12.70	-	3.00	VIS-NIR (400-1000nm)	#15-435	A\$143.38 Volume Pricing	20+ In Stock
12.70	-	3.00	VIS 0° (425-675nm)	#15-431	A\$137.61 Volume Pricing	3 In Stock
12.70	-	3.00	YAG-BBAR (500-1100nm)	#15-791	A\$143.38 Volume Pricing	11 In Stock
12.70	-	3.00	NIR I (600-1050nm)	#15-439	A\$137.61 Volume Pricing	7 In Stock
12.70	-	3.00	NIR II (750-1550nm)	#25-795	A\$137.61 Volume Pricing	2 In Stock
15.00	-	1.00	Uncoated	#20-503	A\$102.18 Volume Pricing	Contact Us
15.00	-	1.00	MgF ₂ (400-700nm)	#23-360	A\$120.30 Volume Pricing	2 In Stock
15.00	-	1.00	VIS-EXT (350-700nm)	#23-448	A\$145.85 Volume Pricing	4 In Stock
15.00	-	1.00	VIS-NIR (400-1000nm)	#23-404	A\$145.85 Volume Pricing	Contact Us
15.00	-	1.00	VIS 0° (425-675nm)	#23-382	A\$140.08 Volume Pricing	5 In Stock
15.00	-	1.00	YAG-BBAR (500-1100nm)	#23-470	A\$145.85 Volume Pricing	4 In Stock
15.00	-	1.00	NIR I (600-1050nm)	#23-426	A\$140.08 Volume Pricing	2 In Stock

15.00	-	1.00	NIR II (750-1550nm)	#25-796	A\$140.08 Volume Pricing	5 In Stock
15.00	-	3.00	Uncoated	#45-575	A\$102.18 Volume Pricing	20+ In Stock
15.00	-	3.00	MgF ₂ (400-700nm)	#45-576	A\$120.30 Volume Pricing	20+ In Stock
15.00	-	3.00	VIS-EXT (350-700nm)	#13-292	A\$145.85 Volume Pricing	6 In Stock
15.00	-	3.00	VIS-NIR (400-1000nm)	#45-659	A\$145.85 Volume Pricing	20+ In Stock
15.00	-	3.00	VIS 0° (425-675nm)	#47-518	A\$140.08 Volume Pricing	20+ In Stock
15.00	-	3.00	YAG-BBAR (500-1100nm)	#13-314	A\$145.85 Volume Pricing	7 In Stock
15.00	-	3.00	NIR I (600-1050nm)	#83-470	A\$140.08 Volume Pricing	9 In Stock
15.00	-	3.00	NIR II (750-1550nm)	#25-797	A\$140.08 Volume Pricing	6 In Stock
20.00	-	1.00	Uncoated	#20-504	A\$108.77 Volume Pricing	20+ In Stock
20.00	-	1.00	MgF ₂ (400-700nm)	#23-361	A\$128.54 Volume Pricing	Contact Us
20.00	-	1.00	VIS-EXT (350-700nm)	#23-449	A\$154.09 Volume Pricing	4 In Stock
20.00	-	1.00	VIS-NIR (400-1000nm)	#23-405	A\$154.09 Volume Pricing	5 In Stock
20.00	-	1.00	VIS 0° (425-675nm)	#23-383	A\$149.97 Volume Pricing	3 In Stock
20.00	-	1.00	YAG-BBAR (500-1100nm)	#23-471	A\$154.09 Volume Pricing	4 In Stock
20.00	-	1.00	NIR I (600-1050nm)	#23-427	A\$149.97 Volume Pricing	5 In Stock
20.00	-	1.00	NIR II (750-1550nm)	#25-798	A\$149.97 Volume Pricing	1 In Stock

20.00	-	2.00	Uncoated	#20-507	A\$108.77 Volume Pricing	20+ In Stock
20.00	-	2.00	MgF ₂ (400-700nm)	#23-362	A\$128.54 Volume Pricing	5 In Stock
20.00	-	2.00	VIS-EXT (350-700nm)	#23-450	A\$154.09 Volume Pricing	4 In Stock
20.00	-	2.00	VIS-NIR (400-1000nm)	#23-406	A\$154.09 Volume Pricing	8 In Stock
20.00	-	2.00	VIS 0° (425-675nm)	#23-384	A\$149.97 Volume Pricing	6 In Stock
20.00	-	2.00	YAG-BBAR (500-1100nm)	#23-472	A\$154.09 Volume Pricing	8 In Stock
20.00	-	2.00	NIR I (600-1050nm)	#23-428	A\$149.97 Volume Pricing	1 In Stock
20.00	-	2.00	NIR II (750-1550nm)	#25-799	A\$149.97 Volume Pricing	3 In Stock
20.00	-	3.00	Uncoated	#45-577	A\$108.77 Volume Pricing	20+ In Stock
20.00	-	3.00	MgF ₂ (400-700nm)	#45-578	A\$128.54 Volume Pricing	3 In Stock
20.00	-	3.00	VIS-EXT (350-700nm)	#13-293	A\$154.09 Volume Pricing	2 In Stock
20.00	-	3.00	VIS-NIR (400-1000nm)	#45-660	A\$154.09 Volume Pricing	20+ In Stock
20.00	-	3.00	VIS 0° (425-675nm)	#47-519	A\$149.97 Volume Pricing	20+ In Stock
20.00	-	3.00	YAG-BBAR (500-1100nm)	#13-315	A\$154.09 Volume Pricing	4 In Stock
20.00	-	3.00	NIR I (600-1050nm)	#83-471	A\$149.97 Volume Pricing	20+ In Stock
20.00	-	3.00	NIR II (750-1550nm)	#25-800	A\$149.97 Volume Pricing	1 In Stock
25.00	-	1.00	Uncoated	#36-991	A\$115.36 Volume Pricing	20+ In Stock

25.00	-	1.00	MgF ₂ (400-700nm)	#36-994	A\$135.96 Volume Pricing	5 In Stock
25.00	-	1.00	VIS-EXT (350-700nm)	#13-294	A\$160.68 Volume Pricing	9 In Stock
25.00	-	1.00	VIS-NIR (400-1000nm)	#36-997	A\$160.68 Volume Pricing	14 In Stock
25.00	-	1.00	VIS 0° (425-675nm)	#36-996	A\$155.74 Volume Pricing	6 In Stock
25.00	-	1.00	YAG-BBAR (500-1100nm)	#13-316	A\$160.68 Volume Pricing	1 In Stock
25.00	-	1.00	NIR I (600-1050nm)	#36-995	A\$155.74 Volume Pricing	14 In Stock
25.00	-	1.00	NIR II (750-1550nm)	#25-801	A\$155.74 Volume Pricing	2 In Stock
25.00	-	1.00	BBAR (1650-3000nm)	#70-281	A\$174.69 Volume Pricing	3 In Stock
-	25.00 x 25.00	1.00	Uncoated	#20-556	A\$115.36 Volume Pricing	20+ In Stock
-	25.00 x 25.00	1.00	MgF ₂ (400-700nm)	#23-370	A\$135.96 Volume Pricing	4 In Stock
-	25.00 x 25.00	1.00	VIS-EXT (350-700nm)	#23-458	A\$160.68 Volume Pricing	Contact Us
-	25.00 x 25.00	1.00	VIS-NIR (400-1000nm)	#23-414	A\$160.68 Volume Pricing	6 In Stock
-	25.00 x 25.00	1.00	VIS 0° (425-675nm)	#23-392	A\$155.74 Volume Pricing	1 In Stock
-	25.00 x 25.00	1.00	YAG-BBAR (500-1100nm)	#23-480	A\$160.68 Volume Pricing	1 In Stock
-	25.00 x 25.00	1.00	NIR I (600-1050nm)	#23-436	A\$155.74 Volume Pricing	5 In Stock
-	25.00 x 25.00	1.00	NIR II (750-1550nm)	#25-802	A\$155.74 Volume Pricing	5 In Stock
25.00	-	2.00	Uncoated	#36-992	A\$115.36 Volume Pricing	20+ In Stock

25.00	-	2.00	MgF ₂ (400-700nm)	#36-998	A\$135.96 Volume Pricing	20+ In Stock
25.00	-	2.00	VIS-EXT (350-700nm)	#13-295	A\$160.68 Volume Pricing	10 In Stock
25.00	-	2.00	VIS-NIR (400-1000nm)	#37-002	A\$160.68 Volume Pricing	3 In Stock
25.00	-	2.00	VIS 0° (425-675nm)	#37-001	A\$155.74 Volume Pricing	7 In Stock
25.00	-	2.00	YAG-BBAR (500-1100nm)	#13-317	A\$160.68 Volume Pricing	6 In Stock
25.00	-	2.00	NIR I (600-1050nm)	#36-999	A\$155.74 Volume Pricing	10 In Stock
25.00	-	2.00	NIR II (750-1550nm)	#25-803	A\$155.74 Volume Pricing	1 In Stock
-	25.00 x 25.00	2.00	Uncoated	#20-573	A\$115.36 Volume Pricing	7 In Stock
-	25.00 x 25.00	2.00	MgF ₂ (400-700nm)	#23-371	A\$135.96 Volume Pricing	1 In Stock
-	25.00 x 25.00	2.00	VIS-EXT (350-700nm)	#23-459	A\$160.68 Volume Pricing	Contact Us
-	25.00 x 25.00	2.00	VIS-NIR (400-1000nm)	#23-415	A\$160.68 Volume Pricing	4 In Stock
-	25.00 x 25.00	2.00	VIS 0° (425-675nm)	#23-393	A\$155.74 Volume Pricing	4 In Stock
-	25.00 x 25.00	2.00	YAG-BBAR (500-1100nm)	#23-481	A\$160.68 Volume Pricing	13 In Stock
-	25.00 x 25.00	2.00	NIR I (600-1050nm)	#23-437	A\$155.74 Volume Pricing	1 In Stock
-	25.00 x 25.00	2.00	NIR II (750-1550nm)	#25-804	A\$155.74 Volume Pricing	2 In Stock
25.00	-	3.00	Uncoated	#36-993	A\$115.36 Volume Pricing	20+ In Stock
25.00	-	3.00	MgF ₂ (400-700nm)	#37-003	A\$135.96 Volume Pricing	Contact Us

25.00	-	3.00	VIS-EXT (350-700nm)	#13-296	A\$160.68 Volume Pricing	5 In Stock
25.00	-	3.00	VIS-NIR (400-1000nm)	#37-006	A\$160.68 Volume Pricing	3 In Stock
25.00	-	3.00	VIS 0° (425-675nm)	#37-005	A\$155.74 Volume Pricing	12 In Stock
25.00	-	3.00	YAG-BBAR (500-1100nm)	#13-318	A\$160.68 Volume Pricing	4 In Stock
25.00	-	3.00	NIR I (600-1050nm)	#37-004	A\$155.74 Volume Pricing	2 In Stock
25.00	-	3.00	NIR II (750-1550nm)	#25-805	A\$155.74 Volume Pricing	8 In Stock
25.00	-	3.00	BBAR (1650-3000nm)	#70-282	A\$174.69 Volume Pricing	3 In Stock
25.00	-	4.00	Uncoated	#45-076	A\$115.36 Volume Pricing	20+ In Stock
25.00	-	4.00	MgF ₂ (400-700nm)	#45-258	A\$135.96 Volume Pricing	2 In Stock
25.00	-	4.00	VIS-EXT (350-700nm)	#13-297	A\$160.68 Volume Pricing	Contact Us
25.00	-	4.00	VIS-NIR (400-1000nm)	#45-661	A\$160.68 Volume Pricing	15 In Stock
25.00	-	4.00	VIS 0° (425-675nm)	#47-520	A\$155.74 Volume Pricing	20+ In Stock
25.00	-	4.00	YAG-BBAR (500-1100nm)	#13-319	A\$160.68 Volume Pricing	12 In Stock
25.00	-	4.00	NIR I (600-1050nm)	#83-472	A\$155.74 Volume Pricing	1 In Stock
25.00	-	4.00	NIR II (750-1550nm)	#25-806	A\$155.74 Volume Pricing	3 In Stock
-	25.00 x 25.00	4.00	Uncoated	#49-622	A\$115.36 Volume Pricing	20+ In Stock
-	25.00 x 25.00	4.00	MgF ₂ (400-700nm)	#49-625	A\$135.96 Volume Pricing	1 In Stock

-	25.00 x 25.00	4.00	VIS-EXT (350-700nm)	#13-298	A\$160.68 Volume Pricing	5 In Stock
-	25.00 x 25.00	4.00	VIS-NIR (400-1000nm)	#49-633	A\$160.68 Volume Pricing	3 In Stock
-	25.00 x 25.00	4.00	VIS 0° (425-675nm)	#49-629	A\$155.74 Volume Pricing	20+ In Stock
-	25.00 x 25.00	4.00	YAG-BBAR (500-1100nm)	#13-320	A\$160.68 Volume Pricing	6 In Stock
-	25.00 x 25.00	4.00	NIR I (600-1050nm)	#83-473	A\$155.74 Volume Pricing	Contact Us
-	25.00 x 25.00	4.00	NIR II (750-1550nm)	#25-807	A\$155.74 Volume Pricing	6 In Stock
-	25.00 x 35.00	3.00	Uncoated	#29-301	A\$120.30 Volume Pricing	20+ In Stock
-	25.20 x 35.60	1.00	Uncoated	#29-302	A\$120.30 Volume Pricing	20+ In Stock
25.40	-	1.00	Uncoated	#20-512	A\$115.36 Volume Pricing	Contact Us
25.40	-	1.00	MgF ₂ (400-700nm)	#23-363	A\$135.96 Volume Pricing	3 In Stock
25.40	-	1.00	VIS-EXT (350-700nm)	#23-451	A\$160.68 Volume Pricing	Contact Us
25.40	-	1.00	VIS-NIR (400-1000nm)	#23-407	A\$160.68 Volume Pricing	Contact Us
25.40	-	1.00	VIS 0° (425-675nm)	#23-385	A\$155.74 Volume Pricing	1 In Stock
25.40	-	1.00	YAG-BBAR (500-1100nm)	#23-473	A\$160.68 Volume Pricing	9 In Stock
25.40	-	1.00	NIR I (600-1050nm)	#23-429	A\$155.74 Volume Pricing	5 In Stock
25.40	-	1.00	NIR II (750-1550nm)	#25-808	A\$155.74 Volume Pricing	1 In Stock
25.40	-	2.00	Uncoated	#15-424	A\$115.36 Volume Pricing	20+ In Stock

25.40	-	2.00	MgF ₂ (400-700nm)	#15-428	A\$135.96 Volume Pricing	1 In Stock
25.40	-	2.00	VIS-EXT (350-700nm)	#15-788	A\$160.68 Volume Pricing	Contact Us
25.40	-	2.00	VIS-NIR (400-1000nm)	#15-436	A\$160.68 Volume Pricing	6 In Stock
25.40	-	2.00	VIS 0° (425-675nm)	#15-432	A\$155.74 Volume Pricing	4 In Stock
25.40	-	2.00	YAG-BBAR (500-1100nm)	#15-792	A\$160.68 Volume Pricing	3 In Stock
25.40	-	2.00	NIR I (600-1050nm)	#15-440	A\$155.74 Volume Pricing	9 In Stock
25.40	-	2.00	NIR II (750-1550nm)	#25-809	A\$155.74 Volume Pricing	3 In Stock
25.40	-	4.00	Uncoated	#15-425	A\$115.36 Volume Pricing	20+ In Stock
25.40	-	4.00	MgF ₂ (400-700nm)	#15-429	A\$135.96 Volume Pricing	3 In Stock
25.40	-	4.00	VIS-EXT (350-700nm)	#15-789	A\$160.68 Volume Pricing	5 In Stock
25.40	-	4.00	VIS-NIR (400-1000nm)	#15-437	A\$160.68 Volume Pricing	6 In Stock
25.40	-	4.00	VIS 0° (425-675nm)	#15-433	A\$155.74 Volume Pricing	3 In Stock
25.40	-	4.00	YAG-BBAR (500-1100nm)	#15-793	A\$160.68 Volume Pricing	3 In Stock
25.40	-	4.00	NIR I (600-1050nm)	#15-441	A\$155.74 Volume Pricing	4 In Stock
25.40	-	4.00	NIR II (750-1550nm)	#25-810	A\$155.74 Volume Pricing	5 In Stock
30.00	-	1.00	Uncoated	#20-528	A\$120.30 Volume Pricing	20+ In Stock
30.00	-	1.00	MgF ₂ (400-700nm)	#23-364	A\$152.44 Volume Pricing	1 In Stock

30.00	-	1.00	VIS-EXT (350-700nm)	#23-452	A\$187.87 Volume Pricing	4 In Stock
30.00	-	1.00	VIS-NIR (400-1000nm)	#23-408	A\$187.87 Volume Pricing	20+ In Stock
30.00	-	1.00	VIS 0° (425-675nm)	#23-386	A\$181.28 Volume Pricing	3 In Stock
30.00	-	1.00	YAG-BBAR (500-1100nm)	#23-474	A\$187.87 Volume Pricing	4 In Stock
30.00	-	1.00	NIR I (600-1050nm)	#23-430	A\$181.28 Volume Pricing	9 In Stock
30.00	-	1.00	NIR II (750-1550nm)	#25-811	A\$181.28 Volume Pricing	1 In Stock
30.00	-	2.00	Uncoated	#20-530	A\$120.30 Volume Pricing	20+ In Stock
30.00	-	2.00	MgF ₂ (400-700nm)	#23-365	A\$152.44 Volume Pricing	4 In Stock
30.00	-	2.00	VIS-EXT (350-700nm)	#23-453	A\$187.87 Volume Pricing	Contact Us
30.00	-	2.00	VIS-NIR (400-1000nm)	#23-409	A\$187.87 Volume Pricing	10 In Stock
30.00	-	2.00	VIS 0° (425-675nm)	#23-387	A\$181.28 Volume Pricing	8 In Stock
30.00	-	2.00	YAG-BBAR (500-1100nm)	#23-475	A\$187.87 Volume Pricing	2 In Stock
30.00	-	2.00	NIR I (600-1050nm)	#23-431	A\$181.28 Volume Pricing	5 In Stock
30.00	-	2.00	NIR II (750-1550nm)	#25-812	A\$181.28 Volume Pricing	7 In Stock
30.00	-	4.00	Uncoated	#45-579	A\$120.30 Volume Pricing	20+ In Stock
30.00	-	4.00	MgF ₂ (400-700nm)	#45-580	A\$152.44 Volume Pricing	14 In Stock
30.00	-	4.00	VIS-EXT (350-700nm)	#13-299	A\$187.87 Volume Pricing	13 In Stock

30.00	-	4.00	VIS-NIR (400-1000nm)	#48-445	A\$187.87 Volume Pricing	20+ In Stock
30.00	-	4.00	VIS 0° (425-675nm)	#47-521	A\$181.28 Volume Pricing	20+ In Stock
30.00	-	4.00	YAG-BBAR (500-1100nm)	#13-321	A\$187.87 Volume Pricing	20+ In Stock
30.00	-	4.00	NIR I (600-1050nm)	#83-474	A\$181.28 Volume Pricing	13 In Stock
30.00	-	4.00	NIR II (750-1550nm)	#25-813	A\$181.28 Volume Pricing	5 In Stock
-	35.00 x 35.00	1.00	Uncoated	#20-584	A\$134.31 Volume Pricing	14 In Stock
-	35.00 x 35.00	1.00	MgF ₂ (400-700nm)	#23-372	A\$164.80 Volume Pricing	Contact Us
-	35.00 x 35.00	1.00	VIS-EXT (350-700nm)	#23-460	A\$196.11 Volume Pricing	3 In Stock
-	35.00 x 35.00	1.00	VIS-NIR (400-1000nm)	#23-416	A\$196.11 Volume Pricing	Contact Us
-	35.00 x 35.00	1.00	VIS 0° (425-675nm)	#23-394	A\$192.82 Volume Pricing	9 In Stock
-	35.00 x 35.00	1.00	YAG-BBAR (500-1100nm)	#23-482	A\$196.11 Volume Pricing	3 In Stock
-	35.00 x 35.00	1.00	NIR I (600-1050nm)	#23-438	A\$192.82 Volume Pricing	1 In Stock
-	35.00 x 35.00	1.00	NIR II (750-1550nm)	#25-814	A\$192.82 Volume Pricing	5 In Stock
-	35.00 x 35.00	2.00	Uncoated	#20-586	A\$134.31 Volume Pricing	20+ In Stock
-	35.00 x 35.00	2.00	MgF ₂ (400-700nm)	#23-373	A\$164.80 Volume Pricing	3 In Stock
-	35.00 x 35.00	2.00	VIS-EXT (350-700nm)	#23-461	A\$196.11 Volume Pricing	11 In Stock
-	35.00 x 35.00	2.00	VIS-NIR (400-1000nm)	#23-417	A\$196.11 Volume Pricing	Contact Us

-	35.00 x 35.00	2.00	VIS 0° (425-675nm)	#23-395	A\$192.82 Volume Pricing	2 In Stock
-	35.00 x 35.00	2.00	YAG-BBAR (500-1100nm)	#23-483	A\$196.11 Volume Pricing	5 In Stock
-	35.00 x 35.00	2.00	NIR I (600-1050nm)	#23-439	A\$192.82 Volume Pricing	2 In Stock
-	35.00 x 35.00	2.00	NIR II (750-1550nm)	#25-815	A\$192.82 Volume Pricing	2 In Stock
-	35.00 x 35.00	3.00	Uncoated	#49-470	A\$134.31 Volume Pricing	20+ In Stock
-	35.00 x 35.00	3.00	MgF ₂ (400-700nm)	#49-626	A\$164.80 Volume Pricing	20+ In Stock
-	35.00 x 35.00	3.00	VIS-EXT (350-700nm)	#13-300	A\$196.11 Volume Pricing	Contact Us
-	35.00 x 35.00	3.00	VIS-NIR (400-1000nm)	#49-634	A\$196.11 Volume Pricing	16 In Stock
-	35.00 x 35.00	3.00	VIS 0° (425-675nm)	#49-630	A\$192.82 Volume Pricing	20+ In Stock
-	35.00 x 35.00	3.00	YAG-BBAR (500-1100nm)	#13-322	A\$196.11 Volume Pricing	6 In Stock
-	35.00 x 35.00	3.00	NIR I (600-1050nm)	#83-475	A\$192.82 Volume Pricing	20+ In Stock
-	35.00 x 35.00	3.00	NIR II (750-1550nm)	#25-816	A\$192.82 Volume Pricing	4 In Stock
40.00	-	1.00	Uncoated	#20-532	A\$148.32 Volume Pricing	20+ In Stock
40.00	-	1.00	MgF ₂ (400-700nm)	#23-366	A\$176.34 Volume Pricing	5 In Stock
40.00	-	1.00	VIS-EXT (350-700nm)	#23-454	A\$207.65 Volume Pricing	5 In Stock
40.00	-	1.00	VIS-NIR (400-1000nm)	#23-410	A\$207.65 Volume Pricing	4 In Stock
40.00	-	1.00	VIS 0° (425-675nm)	#23-388	A\$204.35 Volume Pricing	8 In Stock

40.00	-	1.00	YAG-BBAR (500-1100nm)	#23-476	A\$207.65 Volume Pricing	3 In Stock
40.00	-	1.00	NIR I (600-1050nm)	#23-432	A\$204.35 Volume Pricing	1 In Stock
40.00	-	1.00	NIR II (750-1550nm)	#25-817	A\$204.35 Volume Pricing	4 In Stock
40.00	-	2.00	Uncoated	#20-536	A\$148.32 Volume Pricing	11 In Stock
40.00	-	2.00	MgF ₂ (400-700nm)	#23-367	A\$176.34 Volume Pricing	5 In Stock
40.00	-	2.00	VIS-EXT (350-700nm)	#23-455	A\$207.65 Volume Pricing	1 In Stock
40.00	-	2.00	VIS-NIR (400-1000nm)	#23-411	A\$207.65 Volume Pricing	Contact Us
40.00	-	2.00	VIS 0° (425-675nm)	#23-389	A\$204.35 Volume Pricing	Contact Us
40.00	-	2.00	YAG-BBAR (500-1100nm)	#23-477	A\$207.65 Volume Pricing	3 In Stock
40.00	-	2.00	NIR I (600-1050nm)	#23-433	A\$204.35 Volume Pricing	3 In Stock
40.00	-	2.00	NIR II (750-1550nm)	#25-818	A\$204.35 Volume Pricing	4 In Stock
40.00	-	4.00	Uncoated	#45-581	A\$148.32 Volume Pricing	20+ In Stock
40.00	-	4.00	MgF ₂ (400-700nm)	#45-582	A\$176.34 Volume Pricing	20+ In Stock
40.00	-	4.00	VIS-EXT (350-700nm)	#13-301	A\$207.65 Volume Pricing	1 In Stock
40.00	-	4.00	VIS-NIR (400-1000nm)	#48-446	A\$207.65 Volume Pricing	20+ In Stock
40.00	-	4.00	VIS 0° (425-675nm)	#47-522	A\$204.35 Volume Pricing	20+ In Stock
40.00	-	4.00	YAG-BBAR (500-1100nm)	#13-323	A\$207.65 Volume Pricing	13 In Stock

40.00	-	4.00	NIR I (600-1050nm)	#83-476	A\$204.35 Volume Pricing	7 In Stock
40.00	-	4.00	NIR II (750-1550nm)	#25-819	A\$204.35 Volume Pricing	5 In Stock
50.00	-	1.00	Uncoated	#34-427	A\$156.56 Volume Pricing	20+ In Stock
50.00	-	1.00	MgF ₂ (400-700nm)	#37-007	A\$189.52 Volume Pricing	Contact Us
50.00	-	1.00	VIS-EXT (350-700nm)	#13-302	A\$215.89 Volume Pricing	3 In Stock
50.00	-	1.00	VIS-NIR (400-1000nm)	#37-010	A\$215.89 Volume Pricing	20+ In Stock
50.00	-	1.00	VIS 0° (425-675nm)	#37-009	A\$212.59 Volume Pricing	4 In Stock
50.00	-	1.00	YAG-BBAR (500-1100nm)	#13-324	A\$215.89 Volume Pricing	5 In Stock
50.00	-	1.00	NIR I (600-1050nm)	#37-008	A\$212.59 Volume Pricing	3 In Stock
50.00	-	1.00	NIR II (750-1550nm)	#25-820	A\$212.59 Volume Pricing	3 In Stock
50.00	-	3.00	BBAR (1650-3000nm)	#70-283	A\$220.83 Volume Pricing	4 In Stock
-	50.00 x 50.00	1.00	Uncoated	#20-592	A\$156.56 Volume Pricing	20+ In Stock
-	50.00 x 50.00	1.00	MgF ₂ (400-700nm)	#23-374	A\$189.52 Volume Pricing	5 In Stock
-	50.00 x 50.00	1.00	VIS-EXT (350-700nm)	#23-462	A\$215.89 Volume Pricing	2 In Stock
-	50.00 x 50.00	1.00	VIS-NIR (400-1000nm)	#23-418	A\$215.89 Volume Pricing	2 In Stock
-	50.00 x 50.00	1.00	VIS 0° (425-675nm)	#23-396	A\$212.59 Volume Pricing	5 In Stock
-	50.00 x 50.00	1.00	YAG-BBAR (500-1100nm)	#23-484	A\$215.89 Volume Pricing	4 In Stock

-	50.00 x 50.00	1.00	NIR I (600-1050nm)	#23-440	A\$212.59 Volume Pricing	3 In Stock
-	50.00 x 50.00	1.00	NIR II (750-1550nm)	#25-821	A\$212.59 Volume Pricing	3 In Stock
50.00	-	2.00	Uncoated	#34-428	A\$156.56 Volume Pricing	20+ In Stock
50.00	-	2.00	MgF ₂ (400-700nm)	#37-011	A\$189.52 Volume Pricing	2 In Stock
50.00	-	2.00	VIS-EXT (350-700nm)	#13-303	A\$215.89 Volume Pricing	2 In Stock
50.00	-	2.00	VIS-NIR (400-1000nm)	#37-014	A\$215.89 Volume Pricing	14 In Stock
50.00	-	2.00	VIS 0° (425-675nm)	#37-013	A\$212.59 Volume Pricing	8 In Stock
50.00	-	2.00	YAG-BBAR (500-1100nm)	#13-325	A\$215.89 Volume Pricing	4 In Stock
50.00	-	2.00	NIR I (600-1050nm)	#37-012	A\$212.59 Volume Pricing	3 In Stock
50.00	-	2.00	NIR II (750-1550nm)	#25-822	A\$212.59 Volume Pricing	3 In Stock
-	50.00 x 50.00	2.00	Uncoated	#20-596	A\$156.56 Volume Pricing	20+ In Stock
-	50.00 x 50.00	2.00	MgF ₂ (400-700nm)	#23-375	A\$189.52 Volume Pricing	2 In Stock
-	50.00 x 50.00	2.00	VIS-EXT (350-700nm)	#23-463	A\$215.89 Volume Pricing	20+ In Stock
-	50.00 x 50.00	2.00	VIS-NIR (400-1000nm)	#23-419	A\$215.89 Volume Pricing	2 In Stock
-	50.00 x 50.00	2.00	VIS 0° (425-675nm)	#23-397	A\$212.59 Volume Pricing	3 In Stock
-	50.00 x 50.00	2.00	YAG-BBAR (500-1100nm)	#23-485	A\$215.89 Volume Pricing	5 In Stock
-	50.00 x 50.00	2.00	NIR I (600-1050nm)	#23-441	A\$212.59 Volume Pricing	5 In Stock

-	50.00 x 50.00	2.00	NIR II (750-1550nm)	#25-823	A\$212.59 Volume Pricing	11 In Stock
50.00	-	3.00	Uncoated	#34-429	A\$156.56 Volume Pricing	20+ In Stock
50.00	-	3.00	MgF ₂ (400-700nm)	#37-015	A\$189.52 Volume Pricing	2 In Stock
50.00	-	3.00	VIS-EXT (350-700nm)	#13-304	A\$215.89 Volume Pricing	9 In Stock
50.00	-	3.00	VIS-NIR (400-1000nm)	#37-018	A\$215.89 Volume Pricing	13 In Stock
50.00	-	3.00	VIS 0° (425-675nm)	#37-017	A\$212.59 Volume Pricing	10 In Stock
50.00	-	3.00	YAG-BBAR (500-1100nm)	#13-326	A\$215.89 Volume Pricing	1 In Stock
50.00	-	3.00	NIR I (600-1050nm)	#37-016	A\$212.59 Volume Pricing	9 In Stock
50.00	-	3.00	NIR II (750-1550nm)	#25-824	A\$212.59 Volume Pricing	5 In Stock
50.00	-	4.00	Uncoated	#45-583	A\$156.56 Volume Pricing	20+ In Stock
50.00	-	4.00	MgF ₂ (400-700nm)	#45-584	A\$189.52 Volume Pricing	20+ In Stock
50.00	-	4.00	VIS-EXT (350-700nm)	#13-305	A\$215.89 Volume Pricing	Contact Us
50.00	-	4.00	VIS-NIR (400-1000nm)	#48-447	A\$215.89 Volume Pricing	20+ In Stock
50.00	-	4.00	VIS 0° (425-675nm)	#47-523	A\$212.59 Volume Pricing	20+ In Stock
50.00	-	4.00	YAG-BBAR (500-1100nm)	#13-327	A\$215.89 Volume Pricing	6 In Stock
50.00	-	4.00	NIR I (600-1050nm)	#83-477	A\$212.59 Volume Pricing	8 In Stock
50.00	-	4.00	NIR II (750-1550nm)	#25-825	A\$212.59 Volume Pricing	20+ In Stock

-	50.00 x 50.00	4.00	Uncoated	#47-944	A\$156.56 Volume Pricing	20+ In Stock
-	50.00 x 50.00	4.00	MgF ₂ (400-700nm)	#47-945	A\$189.52 Volume Pricing	1 In Stock
-	50.00 x 50.00	4.00	VIS-EXT (350-700nm)	#13-307	A\$215.89 Volume Pricing	8 In Stock
-	50.00 x 50.00	4.00	VIS-NIR (400-1000nm)	#47-947	A\$215.89 Volume Pricing	16 In Stock
-	50.00 x 50.00	4.00	VIS 0° (425-675nm)	#47-946	A\$212.59 Volume Pricing	4 In Stock
-	50.00 x 50.00	4.00	YAG-BBAR (500-1100nm)	#13-329	A\$215.89 Volume Pricing	11 In Stock
-	50.00 x 50.00	4.00	NIR I (600-1050nm)	#83-478	A\$212.59 Volume Pricing	14 In Stock
-	50.00 x 50.00	4.00	NIR II (750-1550nm)	#25-826	A\$212.59 Volume Pricing	2 In Stock
50.00	-	6.00	Uncoated	#34-430	A\$156.56 Volume Pricing	20+ In Stock
50.00	-	6.00	MgF ₂ (400-700nm)	#37-019	A\$189.52 Volume Pricing	6 In Stock
50.00	-	6.00	VIS-EXT (350-700nm)	#13-306	A\$215.89 Volume Pricing	5 In Stock
50.00	-	6.00	VIS-NIR (400-1000nm)	#37-022	A\$215.89 Volume Pricing	8 In Stock
50.00	-	6.00	VIS 0° (425-675nm)	#37-021	A\$212.59 Volume Pricing	3 In Stock
50.00	-	6.00	YAG-BBAR (500-1100nm)	#13-328	A\$215.89 Volume Pricing	11 In Stock
50.00	-	6.00	NIR I (600-1050nm)	#37-020	A\$212.59 Volume Pricing	5 In Stock
50.00	-	6.00	NIR II (750-1550nm)	#25-827	A\$212.59 Volume Pricing	4 In Stock
50.80	-	4.00	Uncoated	#15-426	A\$156.56 Volume Pricing	14 In Stock

50.80	-	4.00	MgF ₂ (400-700nm)	#15-430	A\$189.52 Volume Pricing	1 In Stock
50.80	-	4.00	VIS-EXT (350-700nm)	#15-790	A\$215.89 Volume Pricing	7 In Stock
50.80	-	4.00	VIS-NIR (400-1000nm)	#15-438	A\$215.89 Volume Pricing	5 In Stock
50.80	-	4.00	VIS 0° (425-675nm)	#15-434	A\$212.59 Volume Pricing	16 In Stock
50.80	-	4.00	YAG-BBAR (500-1100nm)	#15-794	A\$215.89 Volume Pricing	3 In Stock
50.80	-	4.00	NIR I (600-1050nm)	#15-442	A\$212.59 Volume Pricing	6 In Stock
50.80	-	4.00	NIR II (750-1550nm)	#25-828	A\$212.59 Volume Pricing	2 In Stock
75.00	-	4.00	BBAR (1650-3000nm)	#70-284	A\$390.58 Volume Pricing	4 In Stock
75.00	-	2.00	Uncoated	#20-538	A\$242.26 Volume Pricing	20+ In Stock
75.00	-	2.00	MgF ₂ (400-700nm)	#23-368	A\$281.81 Volume Pricing	20+ In Stock
75.00	-	2.00	VIS-EXT (350-700nm)	#23-456	A\$346.08 Volume Pricing	7 In Stock
75.00	-	2.00	VIS-NIR (400-1000nm)	#23-412	A\$346.08 Volume Pricing	Contact Us
75.00	-	2.00	VIS 0° (425-675nm)	#23-390	A\$337.84 Volume Pricing	2 In Stock
75.00	-	2.00	YAG-BBAR (500-1100nm)	#23-478	A\$346.08 Volume Pricing	15 In Stock
75.00	-	2.00	NIR I (600-1050nm)	#23-434	A\$337.84 Volume Pricing	4 In Stock
75.00	-	2.00	NIR II (750-1550nm)	#25-829	A\$337.84 Volume Pricing	9 In Stock
-	75.00 x 75.00	2.00	Uncoated	#20-598	A\$242.26 Volume Pricing	20+ In Stock

-	75.00 x 75.00	2.00	MgF ₂ (400-700nm)	#23-376	A\$281.81 Volume Pricing	5 In Stock
-	75.00 x 75.00	2.00	VIS-EXT (350-700nm)	#23-464	A\$346.08 Volume Pricing	5 In Stock
-	75.00 x 75.00	2.00	VIS-NIR (400-1000nm)	#23-420	A\$346.08 Volume Pricing	20+ In Stock
-	75.00 x 75.00	2.00	VIS 0° (425-675nm)	#23-398	A\$337.84 Volume Pricing	12 In Stock
-	75.00 x 75.00	2.00	YAG-BBAR (500-1100nm)	#23-486	A\$346.08 Volume Pricing	15 In Stock
-	75.00 x 75.00	2.00	NIR I (600-1050nm)	#23-442	A\$337.84 Volume Pricing	2 In Stock
-	75.00 x 75.00	2.00	NIR II (750-1550nm)	#25-830	A\$337.84 Volume Pricing	7 In Stock
75.00	-	4.00	Uncoated	#62-606	A\$242.26 Volume Pricing	20+ In Stock
75.00	-	4.00	MgF ₂ (400-700nm)	#62-608	A\$281.81 Volume Pricing	20+ In Stock
75.00	-	4.00	VIS-EXT (350-700nm)	#15-795	A\$346.08 Volume Pricing	10 In Stock
75.00	-	4.00	VIS-NIR (400-1000nm)	#84-359	A\$346.08 Volume Pricing	20+ In Stock
75.00	-	4.00	VIS 0° (425-675nm)	#37-070	A\$337.84 Volume Pricing	5 In Stock
75.00	-	4.00	YAG-BBAR (500-1100nm)	#15-797	A\$346.08 Volume Pricing	Contact Us
75.00	-	4.00	NIR I (600-1050nm)	#37-073	A\$337.84 Volume Pricing	3 In Stock
75.00	-	4.00	NIR II (750-1550nm)	#25-831	A\$337.84 Volume Pricing	20+ In Stock
-	75.00 x 75.00	4.00	Uncoated	#62-607	A\$242.26 Volume Pricing	20+ In Stock
-	75.00 x 75.00	4.00	MgF ₂ (400-700nm)	#62-609	A\$281.81 Volume Pricing	20+ In Stock

-	75.00 x 75.00	4.00	VIS-EXT (350-700nm)	#15-796	A\$346.08 Volume Pricing	20+ In Stock
-	75.00 x 75.00	4.00	VIS-NIR (400-1000nm)	#37-072	A\$346.08 Volume Pricing	9 In Stock
-	75.00 x 75.00	4.00	VIS 0° (425-675nm)	#37-071	A\$337.84 Volume Pricing	3 In Stock
-	75.00 x 75.00	4.00	YAG-BBAR (500-1100nm)	#15-798	A\$346.08 Volume Pricing	5 In Stock
-	75.00 x 75.00	4.00	NIR I (600-1050nm)	#37-074	A\$337.84 Volume Pricing	1 In Stock
-	75.00 x 75.00	4.00	NIR II (750-1550nm)	#25-832	A\$337.84 Volume Pricing	5 In Stock
100.00	-	6.00	Uncoated	#11-856	A\$355.97 Volume Pricing	20+ In Stock
-	100 x 100	6.00	Uncoated	#70-699	A\$355.97 Volume Pricing	Contact Us
100.00	-	6.00	MgF ₂ (400-700nm)	#11-859	A\$641.07 Volume Pricing	5 In Stock
100.00	-	6.00	VIS-NIR (400-1000nm)	#26-675	A\$865.20 Volume Pricing	Contact Us
100.00	-	6.00	VIS 0° (425-675nm)	#17-298	A\$832.24 Volume Pricing	7 In Stock
100.00	-	6.00	VIS-EXT (350-700nm)	#29-590	A\$881.68 Volume Pricing	3 In Stock
100.00	-	6.00	NIR I (600-1050nm)	#17-295	A\$832.24 Volume Pricing	3 In Stock
100.00	-	6.00	NIR II (750-1550nm)	#29-589	A\$881.68 Volume Pricing	3 In Stock
100.00	-	6.00	YAG-BBAR (500-1100nm)	#29-591	A\$881.68 Volume Pricing	1 In Stock
125.00	-	8.00	Uncoated	#11-857	A\$529.01 Volume Pricing	20+ In Stock
125.00	-	8.00	MgF ₂ (400-700nm)	#11-860	A\$814.11 Volume Pricing	6 In Stock

125.00	-	8.00	VIS-NIR (400-1000nm)	#26-676	A\$1,038.24 Volume Pricing	3 In Stock
125.00	-	8.00	VIS 0° (425-675nm)	#17-299	A\$1,005.28 Volume Pricing	13 In Stock
125.00	-	8.00	VIS-EXT (350-700nm)	#29-593	A\$1,062.96 Volume Pricing	Contact Us
125.00	-	8.00	NIR I (600-1050nm)	#17-296	A\$1,005.28 Volume Pricing	2 In Stock
125.00	-	8.00	NIR II (750-1550nm)	#29-592	A\$1,030.00 Volume Pricing	2 In Stock
125.00	-	8.00	YAG-BBAR (500-1100nm)	#29-594	A\$1,062.96 Volume Pricing	1 In Stock
150.00	-	10.00	Uncoated	#11-858	A\$753.14 Volume Pricing	5 In Stock
150.00	-	10.00	MgF ₂ (400-700nm)	#11-861	A\$1,038.24 Volume Pricing	3 In Stock
150.00	-	10.00	VIS-NIR (400-1000nm)	#26-677	A\$1,268.96 Volume Pricing	Contact Us
150.00	-	10.00	VIS 0° (425-675nm)	#17-300	A\$1,236.00 Volume Pricing	3 In Stock
150.00	-	10.00	VIS-EXT (350-700nm)	#29-596	A\$1,293.68 Volume Pricing	1 In Stock
150.00	-	10.00	NIR I (600-1050nm)	#17-297	A\$1,236.00 Volume Pricing	8 In Stock
150.00	-	10.00	NIR II (750-1550nm)	#29-595	A\$1,252.48 Volume Pricing	Contact Us
150.00	-	10.00	YAG-BBAR (500-1100nm)	#29-597	A\$1,293.68 Volume Pricing	2 In Stock
200.00	-	10.00	Uncoated	#26-475	A\$1,087.68 Volume Pricing	5 In Stock
200.00	-	10.00	MgF ₂ (400-700nm)	#29-598	A\$1,763.36 Volume Pricing	1 In Stock
200.00	-	10.00	VIS 0° (425-675nm)	#26-679	A\$1,648.00 Volume Pricing	1 In Stock

200.00	-	10.00	VIS-EXT (350-700nm)	#29-601	A\$2,035.28 Volume Pricing	1 In Stock
200.00	-	10.00	VIS-NIR (400-1000nm)	#29-602	A\$2,035.28 Volume Pricing	Contact Us
200.00	-	10.00	NIR I (600-1050nm)	#29-599	A\$1,944.64 Volume Pricing	3 In Stock
200.00	-	10.00	NIR II (750-1550nm)	#29-600	A\$1,944.64 Volume Pricing	3 In Stock
200.00	-	10.00	YAG-BBAR (500-1100nm)	#29-603	A\$2,035.28 Volume Pricing	2 In Stock
250.00	-	12.50	Uncoated	#29-936	A\$2,414.32 Volume Pricing	5 In Stock
300.00	-	15.00	Uncoated	#29-937	A\$2,859.28 Volume Pricing	4 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com