

[All Products](#) / [Imaging Lenses](#) / [M12 Lenses \(S-Mount Lenses\)](#)

TECHSPEC® HEO Series M12 Lenses



- Up to 1/2", S-Mount Lens
- Up to 1.2 MegaPixels, 5µm Pixel Size Sensors
- Meets IEC Ingress Protection Ratings of IPX7 and IPX9K
- 2.2mm to 8mm Focal Length

Common Specifications

General			
Series:	HEO Series	IR Cut Filter:	No
Imaging Lens Type:	Meets IEC IPX7 and IPX9K		
Physical & Mechanical Properties			
Iris Option:	Fixed		
Weight (g):	4		
Optical Properties			
Working Distance (mm):	400 - ∞		
Sensor			
Pixel Size (µm):	5.00		
Threading & Mounting			
Filter Thread:	N/A		
Mount:	S-Mount (M12 x 0.5)		
Environmental & Durability Factors			
Environmental Rating:	IPX7 and IPX9K		
Type of Ruggedization:	Waterproof (IPX7 and IPX9K)		

Technical Information

Products

FL (mm)	Aperture (f/#)	Max. Sensor Format	WD (mm)	Wavelength	Stock Number	Price	Buy
2.20	f/2	1/3"	400 - ∞	VIS	#58-840	A\$231.00	20+ In Stock
3.60	f/2.5	1/3"	400 - ∞	VIS	#58-841	A\$231.00	9 In Stock
8.00	f/2.5	1/1.7"	400 - ∞	VIS	#63-759	A\$231.00	Contact Us
2.20	f/2	1/3"	400 - ∞	NIR	#58-844	A\$231.00	Contact Us
3.60	f/2.5	1/3"	400 - ∞	NIR	#58-845	A\$231.00	1 In Stock
8.00	f/2.5	1/2"	400 - ∞	NIR	#63-761	A\$231.00	3 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com