

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Precision Polished Metal Coatings](#)

TECHSPEC® $\lambda/10$ First Surface Mirrors



- Precision Fused Silica Substrate
- Variety of Sizes and Coating Options Available
- Low Coefficient of Thermal Expansion

Common Specifications

Physical & Mechanical Properties

Back Surface:	Commercial Polish	Bevel:	Protective as needed
Clear Aperture (%):	90	Edges:	Ground

Optical Properties

Surface Flatness (P-V):	$\lambda/10$	Surface Quality:	20-10
--------------------------------	--------------	-------------------------	-------

Technical Information

Products

Dia. (mm)	Surface Flatness (P-V)	Dimensions (mm)	Thickness (mm)	Coating	Coating Specification	Stock Number	Price	Buy
5.00	$\lambda/10$	-	2.00	Enhanced Aluminum (450- 650nm)	R_{avg} >95% @ 450 - 650nm	#64-007	A\$148.00 Volume Pricing	1 In Stock
5.00	$\lambda/10$	-	2.00	Enhanced Aluminum (250- 700nm)	R_{avg} >89% @ 250 - 450nm R_{avg} >85% @ 250 - 700nm	#68-307	A\$148.00 Volume Pricing	5 In Stock
5.00	$\lambda/10$	-	2.00	Protected Gold (700- 10000nm)	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	#64-021	A\$184.00 Volume Pricing	Contact Us
5.00	$\lambda/10$	-	2.00	Protected Silver (450- 10000nm)	R_{avg} >98% @ 450 - 800nm R_{avg} >98.5% @ 2000 - 10,000nm	#68-321	A\$177.60 Volume Pricing	16 In Stock
5.00	$\lambda/10$	-	2.00	Ultrafast- Enhanced Silver (600- 1000nm)	R_{avg} >99% @ 600 - 1000nm, 0° R_s >99% @ 540 - 1000nm, 45° R_p >98.5% @ ~730 - 870nm, 45°	#21-976	A\$174.40 Volume Pricing	14 In Stock
5.00	$\lambda/10$	-	2.00	Ultrafast- Enhanced Silver (800- 1150nm)	R_{avg} >99% @ 850 - 1150nm, 0° R_s >99% @ 800 - 1150nm, 45° R_p >98.5% @ ~850 - 1100nm, 45°	#22-006	A\$174.40 Volume Pricing	7 In Stock
-	$\lambda/10$	5.0 x 5.0	2.00	Enhanced Aluminum (450- 650nm)	R_{avg} >95% @ 450 - 650nm	#64-008	A\$148.00 Volume Pricing	20+ In Stock
-	$\lambda/10$	5.0 x 5.0	2.00	Enhanced Aluminum (250- 700nm)	R_{avg} >89% @ 250 - 450nm R_{avg} >85% @ 250 - 700nm	#68-308	A\$148.00 Volume Pricing	3 In Stock

-	$\lambda/10$	5.0 x 5.0	2.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-022	A\$184.00 Volume Pricing	1 In Stock
-	$\lambda/10$	5.0 x 5.0	2.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-322	A\$177.60 Volume Pricing	Contact Us
-	$\lambda/10$	5.0 x 5.0	2.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-977	A\$174.40 Volume Pricing	8 In Stock
-	$\lambda/10$	5.0 x 5.0	2.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-007	A\$174.40 Volume Pricing	2 In Stock
6.35	$\lambda/10$	-	4.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#39-189	A\$148.00 Volume Pricing	3 In Stock
6.35	$\lambda/10$	-	4.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#39-188	A\$148.00 Volume Pricing	3 In Stock
6.35	$\lambda/10$	-	4.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#39-186	A\$184.00 Volume Pricing	Contact Us
6.35	$\lambda/10$	-	4.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#39-187	A\$177.60 Volume Pricing	2 In Stock
10.00	$\lambda/10$	-	2.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-009	A\$148.00 Volume Pricing	20+ In Stock

10.00	$\lambda/10$	-	2.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-309	A\$148.00 Volume Pricing	2 In Stock
10.00	$\lambda/10$	-	2.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-023	A\$184.00 Volume Pricing	2 In Stock
10.00	$\lambda/10$	-	2.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-323	A\$177.60 Volume Pricing	20+ In Stock
10.00	$\lambda/10$	-	2.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} > 90\%$ @ 350 - 400nm $R_{avg} > 96\%$ @ 400 - 3,000nm	#70-233	A\$179.20 Volume Pricing	17 In Stock
10.00	$\lambda/10$	-	2.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-979	A\$160.68 Volume Pricing	4 In Stock
10.00	$\lambda/10$	-	2.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-009	A\$174.40 Volume Pricing	3 In Stock
-	$\lambda/10$	10.0 x 10.0	2.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-010	A\$148.00 Volume Pricing	15 In Stock
-	$\lambda/10$	10.0 x 10.0	2.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-310	A\$148.00 Volume Pricing	14 In Stock
-	$\lambda/10$	10.0 x 10.0	2.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-024	A\$163.15 Volume Pricing	15 In Stock

-	$\lambda/10$	10.0 x 10.0	2.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-324	A\$177.60 Volume Pricing	11 In Stock
12.50	$\lambda/10$	-	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#84-409	A\$148.00 Volume Pricing	20+ In Stock
12.50	$\lambda/10$	-	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#84-419	A\$148.00 Volume Pricing	9 In Stock
12.50	$\lambda/10$	-	3.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#84-429	A\$184.00 Volume Pricing	20+ In Stock
12.50	$\lambda/10$	-	3.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#84-439	A\$177.60 Volume Pricing	15 In Stock
12.50	$\lambda/10$	-	3.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} > 90\%$ @ 350 - 400nm $R_{avg} > 96\%$ @ 400 - 3,000nm	#70-234	A\$184.00 Volume Pricing	5 In Stock
12.50	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-980	A\$174.40 Volume Pricing	9 In Stock
12.50	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-010	A\$174.40 Volume Pricing	3 In Stock
-	$\lambda/10$	12.5 x 12.5	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#84-410	A\$148.00 Volume Pricing	3 In Stock
-	$\lambda/10$	12.5 x 12.5	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#84-420	A\$148.00 Volume Pricing	Contact Us

-	$\lambda/10$	12.5 x 12.5	3.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#84-430	A\$184.00 Volume Pricing	13 In Stock
-	$\lambda/10$	12.5 x 12.5	3.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-440	A\$177.60 Volume Pricing	8 In Stock
12.70	$\lambda/10$	-	6.35	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#39-196	A\$144.00 Volume Pricing	1 In Stock
12.70	$\lambda/10$	-	6.35	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#39-195	A\$148.00 Volume Pricing	Contact Us
12.70	$\lambda/10$	-	6.35	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#39-193	A\$184.00 Volume Pricing	1 In Stock
12.70	$\lambda/10$	-	6.35	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#39-194	A\$177.60 Volume Pricing	11 In Stock
15.00	$\lambda/10$	-	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-011	A\$159.20 Volume Pricing	7 In Stock
15.00	$\lambda/10$	-	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-311	A\$159.20 Volume Pricing	4 In Stock
15.00	$\lambda/10$	-	3.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-025	A\$195.20 Volume Pricing	2 In Stock
15.00	$\lambda/10$	-	3.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-325	A\$192.00 Volume Pricing	20+ In Stock
15.00	$\lambda/10$	-	3.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} >90\%$ @ 350 - 400nm $R_{avg} >96\%$ @ 400 - 3,000nm	#70-235	A\$214.40 Volume Pricing	1 In Stock

15.00	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-982	A\$187.20 Volume Pricing	5 In Stock
15.00	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-012	A\$187.20 Volume Pricing	7 In Stock
-	$\lambda/10$	15.0 x 15.0	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-012	A\$159.20 Volume Pricing	5 In Stock
-	$\lambda/10$	15.0 x 15.0	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-312	A\$172.80 Volume Pricing	Contact Us
-	$\lambda/10$	15.0 x 15.0	3.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-026	A\$195.20 Volume Pricing	20+ In Stock
-	$\lambda/10$	15.0 x 15.0	3.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-326	A\$192.00 Volume Pricing	20+ In Stock
-	$\lambda/10$	15.0 x 15.0	3.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-997	A\$187.20 Volume Pricing	6 In Stock
19.10	$\lambda/10$	-	6.35	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#39-203	A\$172.80 Volume Pricing	5 In Stock
19.10	$\lambda/10$	-	6.35	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#39-202	A\$172.80 Volume Pricing	3 In Stock

19.10	$\lambda/10$	-	6.35	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#39-200	A\$214.40 Volume Pricing	2 In Stock
19.10	$\lambda/10$	-	6.35	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#39-201	A\$200.00 Volume Pricing	3 In Stock
20.00	$\lambda/10$	-	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-013	A\$172.80 Volume Pricing	20+ In Stock
20.00	$\lambda/10$	-	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-313	A\$172.80 Volume Pricing	5 In Stock
20.00	$\lambda/10$	-	3.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-027	A\$189.52 Volume Pricing	15 In Stock
20.00	$\lambda/10$	-	3.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-327	A\$200.00 Volume Pricing	20+ In Stock
20.00	$\lambda/10$	-	3.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} >90\%$ @ 350 - 400nm $R_{avg} >96\%$ @ 400 - 3,000nm	#70-236	A\$208.00 Volume Pricing	7 In Stock
20.00	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} >99\%$ @ 600 - 1000nm, 0° $R_s >99\%$ @ 540 - 1000nm, 45° $R_p >98.5\%$ @ ~730 - 870nm, 45°	#21-984	A\$200.00 Volume Pricing	10 In Stock
20.00	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} >99\%$ @ 850 - 1150nm, 0° $R_s >99\%$ @ 800 - 1150nm, 45° $R_p >98.5\%$ @ ~850 - 1100nm, 45°	#22-014	A\$200.00 Volume Pricing	2 In Stock

-	$\lambda/10$	20.0 x 20.0	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-014	A\$172.80 Volume Pricing	Contact Us
-	$\lambda/10$	20.0 x 20.0	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-314	A\$172.80 Volume Pricing	20+ In Stock
-	$\lambda/10$	20.0 x 20.0	3.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-028	A\$214.40 Volume Pricing	Contact Us
-	$\lambda/10$	20.0 x 20.0	3.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-328	A\$177.16 Volume Pricing	20+ In Stock
-	$\lambda/10$	20.0 x 20.0	3.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} >99\%$ @ 600 - 1000nm, 0° $R_s >99\%$ @ 540 - 1000nm, 45° $R_p >98.5\%$ @ ~730 - 870nm, 45°	#21-998	A\$200.00 Volume Pricing	3 In Stock
25.00	$\lambda/10$	-	4.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-015	A\$182.40 Volume Pricing	Contact Us
25.00	$\lambda/10$	-	4.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-315	A\$182.40 Volume Pricing	8 In Stock
25.00	$\lambda/10$	-	4.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-029	A\$251.20 Volume Pricing	20+ In Stock
25.00	$\lambda/10$	-	4.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-329	A\$206.00 Volume Pricing	20+ In Stock
25.00	$\lambda/10$	-	4.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} >90\%$ @ 350 - 400nm $R_{avg} >96\%$ @ 400 - 3,000nm	#70-237	A\$240.00 Volume Pricing	5 In Stock

25.00	$\lambda/10$	-	4.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-985	A\$230.40 Volume Pricing	12 In Stock
25.00	$\lambda/10$	-	4.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-015	A\$230.40 Volume Pricing	14 In Stock
-	$\lambda/10$	25.0 x 25.0	4.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-016	A\$182.40 Volume Pricing	20+ In Stock
-	$\lambda/10$	25.0 x 25.0	4.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-316	A\$182.40 Volume Pricing	20+ In Stock
-	$\lambda/10$	25.0 x 25.0	4.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-030	A\$251.20 Volume Pricing	1 In Stock
-	$\lambda/10$	25.0 x 25.0	4.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-330	A\$233.60 Volume Pricing	16 In Stock
-	$\lambda/10$	25.0 x 35.0	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#25-549	A\$307.20 Volume Pricing	9 In Stock
-	$\lambda/10$	25.0 x 25.0	4.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-999	A\$230.40 Volume Pricing	4 In Stock
25.40	$\lambda/10$	-	6.35	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#39-210	A\$182.40 Volume Pricing	8 In Stock

25.40	$\lambda/10$	-	6.35	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#39-209	A\$177.60 Volume Pricing	Contact Us
25.40	$\lambda/10$	-	6.35	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#39-207	A\$251.20 Volume Pricing	14 In Stock
25.40	$\lambda/10$	-	6.35	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#39-208	A\$206.00 Volume Pricing	20+ In Stock
30.00	$\lambda/10$	-	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#84-411	A\$233.60 Volume Pricing	Contact Us
30.00	$\lambda/10$	-	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#84-421	A\$233.60 Volume Pricing	5 In Stock
30.00	$\lambda/10$	-	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#84-431	A\$316.80 Volume Pricing	14 In Stock
30.00	$\lambda/10$	-	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#84-441	A\$251.20 Volume Pricing	6 In Stock
30.00	$\lambda/10$	-	5.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} > 90\%$ @ 350 - 400nm $R_{avg} > 96\%$ @ 400 - 3,000nm	#70-238	A\$262.40 Volume Pricing	13 In Stock
30.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-987	A\$257.60 Volume Pricing	3 In Stock

30.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\% @ 850 - 1150nm, 0^\circ$ $R_s > 99\% @ 800 - 1150nm, 45^\circ$ $R_p > 98.5\% @ \sim 850 - 1100nm, 45^\circ$	#22-017	A\$257.60 Volume Pricing	2 In Stock
-	$\lambda/10$	30.0 x 30.0	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\% @ 450 - 650nm$	#84-412	A\$233.60 Volume Pricing	20+ In Stock
-	$\lambda/10$	30.0 x 30.0	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	#84-422	A\$233.60 Volume Pricing	Contact Us
-	$\lambda/10$	30.0 x 30.0	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	#84-432	A\$316.80 Volume Pricing	Contact Us
-	$\lambda/10$	30.0 x 30.0	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	#84-442	A\$251.20 Volume Pricing	4 In Stock
-	$\lambda/10$	30.0 x 30.0	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\% @ 600 - 1000nm, 0^\circ$ $R_s > 99\% @ 540 - 1000nm, 45^\circ$ $R_p > 98.5\% @ \sim 730 - 870nm, 45^\circ$	#22-000	A\$257.60 Volume Pricing	1 In Stock
35.00	$\lambda/10$	-	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\% @ 450 - 650nm$	#84-413	A\$260.80 Volume Pricing	20+ In Stock
35.00	$\lambda/10$	-	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	#84-423	A\$260.80 Volume Pricing	6 In Stock
35.00	$\lambda/10$	-	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	#84-433	A\$336.00 Volume Pricing	Contact Us

35.00	$\lambda/10$	-	5.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-443	A\$307.20 Volume Pricing	20+ In Stock
35.00	$\lambda/10$	-	5.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} >90\%$ @ 350 - 400nm $R_{avg} >96\%$ @ 400 - 3,000nm	#70-239	A\$326.40 Volume Pricing	10 In Stock
35.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} >99\%$ @ 600 - 1000nm, 0° $R_s >99\%$ @ 540 - 1000nm, 45° $R_p >98.5\%$ @ ~730 - 870nm, 45°	#21-988	A\$302.40 Volume Pricing	7 In Stock
-	$\lambda/10$	25.0 x 35.0	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#25-546	A\$260.80 Volume Pricing	4 In Stock
-	$\lambda/10$	25.0 x 35.0	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#25-547	A\$260.80 Volume Pricing	1 In Stock
-	$\lambda/10$	25.0 x 35.0	5.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#25-548	A\$336.00 Volume Pricing	14 In Stock
-	$\lambda/10$	35.0 x 35.0	5.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} >99\%$ @ 850 - 1150nm, 0° $R_s >99\%$ @ 800 - 1150nm, 45° $R_p >98.5\%$ @ ~850 - 1100nm, 45°	#22-031	A\$302.40 Volume Pricing	5 In Stock
35.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} >99\%$ @ 850 - 1150nm, 0° $R_s >99\%$ @ 800 - 1150nm, 45° $R_p >98.5\%$ @ ~850 - 1100nm, 45°	#22-018	A\$302.40 Volume Pricing	4 In Stock
-	$\lambda/10$	35.0 x 35.0	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#84-414	A\$260.80 Volume Pricing	14 In Stock

-	$\lambda/10$	35.0 x 35.0	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#84-424	A\$260.80 Volume Pricing	8 In Stock
-	$\lambda/10$	35.0 x 35.0	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#84-434	A\$336.00 Volume Pricing	1 In Stock
-	$\lambda/10$	35.0 x 35.0	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#84-444	A\$307.20 Volume Pricing	20+ In Stock
-	$\lambda/10$	35.0 x 35.0	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#22-001	A\$302.40 Volume Pricing	4 In Stock
38.10	$\lambda/10$	-	6.35	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#39-217	A\$280.00 Volume Pricing	3 In Stock
38.10	$\lambda/10$	-	6.35	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#39-216	A\$280.00 Volume Pricing	20+ In Stock
38.10	$\lambda/10$	-	6.35	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#39-214	A\$371.20 Volume Pricing	1 In Stock
38.10	$\lambda/10$	-	6.35	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#39-215	A\$345.60 Volume Pricing	3 In Stock
40.00	$\lambda/10$	-	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-017	A\$280.00 Volume Pricing	Contact Us
40.00	$\lambda/10$	-	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-317	A\$280.00 Volume Pricing	5 In Stock

40.00	$\lambda/10$	-	5.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-031	A\$371.20 Volume Pricing	16 In Stock
40.00	$\lambda/10$	-	5.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-331	A\$345.60 Volume Pricing	20+ In Stock
40.00	$\lambda/10$	-	5.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} >90\%$ @ 350 - 400nm $R_{avg} >96\%$ @ 400 - 3,000nm	#70-240	A\$372.80 Volume Pricing	12 In Stock
40.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} >99\%$ @ 600 - 1000nm, 0° $R_s >99\%$ @ 540 - 1000nm, 45° $R_p >98.5\%$ @ ~730 - 870nm, 45°	#21-990	A\$337.60 Volume Pricing	5 In Stock
40.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} >99\%$ @ 850 - 1150nm, 0° $R_s >99\%$ @ 800 - 1150nm, 45° $R_p >98.5\%$ @ ~850 - 1100nm, 45°	#22-020	A\$337.60 Volume Pricing	3 In Stock
-	$\lambda/10$	40.0 x 40.0	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-018	A\$280.00 Volume Pricing	9 In Stock
-	$\lambda/10$	40.0 x 40.0	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-318	A\$280.00 Volume Pricing	2 In Stock
-	$\lambda/10$	40.0 x 40.0	5.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-032	A\$371.20 Volume Pricing	11 In Stock
-	$\lambda/10$	40.0 x 40.0	5.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-332	A\$345.60 Volume Pricing	14 In Stock

50.00	$\lambda/10$	-	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-019	A\$307.20 Volume Pricing	20+ In Stock
50.00	$\lambda/10$	-	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-319	A\$307.20 Volume Pricing	Contact Us
50.00	$\lambda/10$	-	5.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-033	A\$411.20 Volume Pricing	2 In Stock
50.00	$\lambda/10$	-	5.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-333	A\$382.40 Volume Pricing	20+ In Stock
50.00	$\lambda/10$	-	5.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} >90\%$ @ 350 - 400nm $R_{avg} >96\%$ @ 400 - 3,000nm	#70-241	A\$427.20 Volume Pricing	14 In Stock
50.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} >99\%$ @ 600 - 1000nm, 0° $R_s >99\%$ @ 540 - 1000nm, 45° $R_p >98.5\%$ @ ~730 - 870nm, 45°	#21-991	A\$374.40 Volume Pricing	8 In Stock
50.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} >99\%$ @ 850 - 1150nm, 0° $R_s >99\%$ @ 800 - 1150nm, 45° $R_p >98.5\%$ @ ~850 - 1100nm, 45°	#22-021	A\$374.40 Volume Pricing	5 In Stock
-	$\lambda/10$	50.0 x 50.0	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-020	A\$307.20 Volume Pricing	9 In Stock
-	$\lambda/10$	50.0 x 50.0	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-320	A\$307.20 Volume Pricing	20+ In Stock
-	$\lambda/10$	50.0 x 50.0	5.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-034	A\$411.20 Volume Pricing	6 In Stock

-	$\lambda/10$	50.0 x 50.0	5.00	Protected Silver (450-10000nm)	R_{avg} >98% @ 450 - 800nm R_{avg} >98.5% @ 2000 - 10,000nm	#68-334	A\$382.40 Volume Pricing	10 In Stock
50.80	$\lambda/10$	-	9.53	Enhanced Aluminum (450-650nm)	R_{avg} >95% @ 450 - 650nm	#39-224	A\$307.20 Volume Pricing	5 In Stock
50.80	$\lambda/10$	-	9.53	Enhanced Aluminum (250-700nm)	R_{avg} >89% @ 250 - 450nm R_{avg} >85% @ 250 - 700nm	#39-223	A\$307.20 Volume Pricing	7 In Stock
50.80	$\lambda/10$	-	9.53	Protected Gold (700-10000nm)	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	#39-221	A\$411.20 Volume Pricing	3 In Stock
50.80	$\lambda/10$	-	9.53	Protected Silver (450-10000nm)	R_{avg} >98% @ 450 - 800nm R_{avg} >98.5% @ 2000 - 10,000nm	#39-222	A\$382.40 Volume Pricing	4 In Stock
75.00	$\lambda/10$	-	7.50	Enhanced Aluminum (450-650nm)	R_{avg} >95% @ 450 - 650nm	#84-415	A\$633.60 Volume Pricing	8 In Stock
75.00	$\lambda/10$	-	7.50	Enhanced Aluminum (250-700nm)	R_{avg} >89% @ 250 - 450nm R_{avg} >85% @ 250 - 700nm	#84-425	A\$560.32 Volume Pricing	5 In Stock
75.00	$\lambda/10$	-	7.50	Protected Gold (700-10000nm)	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	#84-435	A\$824.00 Volume Pricing	8 In Stock
75.00	$\lambda/10$	-	7.50	Protected Silver (450-10000nm)	R_{avg} >98% @ 450 - 800nm R_{avg} >98.5% @ 2000 - 10,000nm	#84-445	A\$764.80 Volume Pricing	20+ In Stock
-	$\lambda/10$	75.0 x 75.0	7.50	Enhanced Aluminum (450-650nm)	R_{avg} >95% @ 450 - 650nm	#84-416	A\$633.60 Volume Pricing	20+ In Stock
-	$\lambda/10$	75.0 x 75.0	7.50	Enhanced Aluminum (250-700nm)	R_{avg} >89% @ 250 - 450nm R_{avg} >85% @ 250 - 700nm	#84-426	A\$633.60 Volume Pricing	7 In Stock

-	$\lambda/10$	75.0 x 75.0	7.50	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#84-436	A\$824.00 Volume Pricing	2 In Stock
-	$\lambda/10$	75.0 x 75.0	7.50	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-446	A\$764.80 Volume Pricing	12 In Stock
100.00	$\lambda/10$	-	10.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#84-417	A\$928.00 Volume Pricing	10 In Stock
100.00	$\lambda/10$	-	10.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#84-427	A\$928.00 Volume Pricing	13 In Stock
100.00	$\lambda/10$	-	10.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#84-437	A\$1,344.00 Volume Pricing	20+ In Stock
100.00	$\lambda/10$	-	10.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-447	A\$1,216.00 Volume Pricing	2 In Stock
-	$\lambda/10$	100.0 x 100.0	10.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#84-418	A\$928.00 Volume Pricing	8 In Stock
-	$\lambda/10$	100.0 x 100.0	10.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#84-428	A\$928.00 Volume Pricing	5 In Stock
-	$\lambda/10$	100.0 x 100.0	10.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#84-438	A\$1,344.00 Volume Pricing	4 In Stock
-	$\lambda/10$	100.0 x 100.0	10.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-448	A\$1,216.00 Volume Pricing	20+ In Stock
5.00	$\lambda/10$	-	1.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#26-094	A\$144.00 Volume Pricing	Contact Us

5.00	$\lambda/10$	-	1.00	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-098	A\$148.00 Volume Pricing	2 In Stock
5.00	$\lambda/10$	-	1.00	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-099	A\$184.00 Volume Pricing	3 In Stock
5.00	$\lambda/10$	-	1.00	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-100	A\$177.60 Volume Pricing	Contact Us
10.00	$\lambda/10$	-	1.00	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-101	A\$148.00 Volume Pricing	1 In Stock
10.00	$\lambda/10$	-	1.00	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-102	A\$148.00 Volume Pricing	5 In Stock
10.00	$\lambda/10$	-	1.00	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-103	A\$184.00 Volume Pricing	Contact Us
10.00	$\lambda/10$	-	1.00	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-104	A\$177.60 Volume Pricing	Contact Us
12.50	$\lambda/10$	-	1.50	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-105	A\$148.00 Volume Pricing	1 In Stock
12.50	$\lambda/10$	-	1.50	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-364	A\$148.00 Volume Pricing	4 In Stock
12.50	$\lambda/10$	-	1.50	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-365	A\$184.00 Volume Pricing	16 In Stock
12.50	$\lambda/10$	-	1.50	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-366	A\$177.60 Volume Pricing	Contact Us
15.00	$\lambda/10$	-	1.50	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-367	A\$159.20 Volume Pricing	5 In Stock

15.00	$\lambda/10$	-	1.50	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-368	A\$159.20 Volume Pricing	Contact Us
15.00	$\lambda/10$	-	1.50	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-369	A\$195.20 Volume Pricing	3 In Stock
15.00	$\lambda/10$	-	1.50	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-370	A\$185.60 Volume Pricing	Contact Us
20.00	$\lambda/10$	-	2.00	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-371	A\$172.80 Volume Pricing	1 In Stock
20.00	$\lambda/10$	-	2.00	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-372	A\$172.80 Volume Pricing	1 In Stock
20.00	$\lambda/10$	-	2.00	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-373	A\$214.40 Volume Pricing	5 In Stock
20.00	$\lambda/10$	-	2.00	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-374	A\$200.00 Volume Pricing	Contact Us
25.00	$\lambda/10$	-	3.00	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-375	A\$182.40 Volume Pricing	2 In Stock
25.00	$\lambda/10$	-	3.00	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-376	A\$182.40 Volume Pricing	5 In Stock
25.00	$\lambda/10$	-	3.00	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-377	A\$251.20 Volume Pricing	2 In Stock
25.00	$\lambda/10$	-	3.00	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-378	A\$233.60 Volume Pricing	2 In Stock
30.00	$\lambda/10$	-	3.00	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-379	A\$233.60 Volume Pricing	1 In Stock

30.00	$\lambda/10$	-	3.00	Enhanced Aluminum (250-700nm)	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	#26-380	A\$233.60 Volume Pricing	4 In Stock
30.00	$\lambda/10$	-	3.00	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	#26-381	A\$316.80 Volume Pricing	3 In Stock
30.00	$\lambda/10$	-	3.00	Protected Silver (450-10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	#26-382	A\$251.20 Volume Pricing	5 In Stock
125.00	$\lambda/10$	-	12.50	Enhanced Aluminum (450-650nm)	R _{avg} >95% @ 450 - 650nm	#70-924	A\$1,584.00 Volume Pricing	1 In Stock
125.00	$\lambda/10$	-	12.50	Enhanced Aluminum (250-700nm)	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	#70-925	A\$1,584.00 Volume Pricing	2 In Stock
125.00	$\lambda/10$	-	12.50	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	#70-926	A\$1,816.00 Volume Pricing	1 In Stock
125.00	$\lambda/10$	-	12.50	Protected Silver (450-10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	#70-927	A\$1,728.00 Volume Pricing	2 In Stock
-	$\lambda/10$	125 x 125	12.50	Enhanced Aluminum (450-650nm)	R _{avg} >95% @ 450 - 650nm	#70-928	A\$1,584.00 Volume Pricing	Contact Us
-	$\lambda/10$	125 x 125	12.50	Enhanced Aluminum (250-700nm)	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	#70-929	A\$1,584.00 Volume Pricing	1 In Stock
-	$\lambda/10$	125 x 125	12.50	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	#70-930	A\$1,816.00 Volume Pricing	4 In Stock
-	$\lambda/10$	125 x 125	12.50	Protected Silver (450-10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	#70-931	A\$1,728.00 Volume Pricing	4 In Stock

150.00	$\lambda/10$	-	15.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#70-932	A\$2,424.00 Volume Pricing	2 In Stock
150.00	$\lambda/10$	-	15.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#70-933	A\$2,424.00 Volume Pricing	3 In Stock
150.00	$\lambda/10$	-	15.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#70-934	A\$2,472.00 Volume Pricing	3 In Stock
150.00	$\lambda/10$	-	15.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 2000nm $R_{avg} >98\%$ @ 2000 - 10,000nm	#70-935	A\$2,608.00 Volume Pricing	Contact Us
-	$\lambda/10$	150 x 150	15.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#70-936	A\$2,424.00 Volume Pricing	3 In Stock
-	$\lambda/10$	150 x 150	15.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#70-937	A\$2,424.00 Volume Pricing	1 In Stock
-	$\lambda/10$	150 x 150	15.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#70-938	A\$2,800.00 Volume Pricing	1 In Stock
-	$\lambda/10$	150 x 150	15.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 2000nm $R_{avg} >98\%$ @ 2000 - 10,000nm	#70-939	A\$2,608.00 Volume Pricing	2 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com