

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Inline Lights](#)

Advanced Illumination In-Line Lights See More by [Advanced Illumination](#)



- Compatible with 8mm or 1/4" (0.312") Fiber Illumination Ports
- Multiple Versions Offered

Common Specifications

General			
LED Lifetime (hours):	50,000	Number of LEDs:	1 High Brightness
Type of Illumination:	LED Illuminator	Manufacturer:	Advanced Illumination
Geometry:	Spot Light		

Physical & Mechanical Properties	
Weight (g):	42.5

Optical Properties	
Light Distribution (%):	±10

Hardware & Interface Connectivity			
Connector:	Flying Leads		
Power Supply:	Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	Length of Cable (m):	1.5

Environmental & Durability Factors	
Operating Temperature (°C):	0 to 60

Technical Information

Products

Color	Wavelength (nm)	Stock Number	Price	Buy
White	-	#66-861	A\$848.00	5 In Stock
White	-	#83-302	A\$1,056.00	Contact Us
Blue	470.00	#66-862	A\$848.00	1 In Stock
Blue	470.00	#83-303	A\$1,056.00	Contact Us
Green	530.00	#66-863	A\$848.00	1 In Stock
Green	530.00	#83-304	A\$1,056.00	Contact Us
Yellow	590.00	#66-864	A\$848.00	Contact Us
Yellow	590.00	#83-305	A\$1,056.00	Contact Us
Red	625.00	#66-865	A\$848.00	1 In Stock
Red	625.00	#83-306	A\$1,056.00	Contact Us



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com