

[All Products](#) / [Test Targets](#) / [Resolution Test Targets](#)

High Resolution Microscopy Slide Targets



- Small Pattern Sizes - 100nm and 3300 lp/mm
- Composed using High-Precision E-Beam Lithography
- Negative Pattern Design

Common Specifications

Physical & Mechanical Properties

Dimensions (mm):	10 x 10 x 1	Construction:	Stainless Steel, 75 x 25 x 1.5mm, microscope slide format
Pattern Tolerance:	100nm/cm = 10^{-5}		

Optical Properties

Substrate:	Fused Silica w/Chrome deposit		
Optical Density OD (Average):	OD>7 @ 400nm, 6 @ 550nm, 4.5 @ 750nm, 3.6 @ 1000nm	Spectral Range:	200 - 2000nm

Technical Information

Products

Title	Stock Number	Price	Buy
High Resolution Microscopy Star Target	#37-538	A\$2,661.52 Volume Pricing	10 In Stock
High Resolution Microscopy Resolution Target	#37-539	A\$2,661.52 Volume Pricing	9 In Stock
High Resolution Microscope Checker Board	#37-540	A\$2,661.52 Volume Pricing	2 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com