

[All Products](#) / [Optics](#) / [IBS \(Ion Beam Sputtering\) Coated Optics](#)

TECHSPEC® High Performance Nd:YAG Laser Line Mirrors



- Up to 99.98% Reflectivity
- Certified High Laser Damage Threshold at DWL up to 15 J/cm² @ 1064nm
- [Superpolished](#) Substrates Available with Parts per Million Level Scattering Performance
- Additional Sizes Coming Soon

Common Specifications

Physical & Mechanical Properties

Back Surface: Commercial Polish

Optical Properties

Coating Type: Dielectric

Substrate: [Fused Silica](#) (Corning 7980)

Technical Information

Products

Wavelength Range (nm)	DWL (nm)	Dia. (mm)	Thickness (mm)	AOI (°)	Stock Number	Price	Buy
-	355	25.40	6.35	45	#34-838	A\$285.10 Volume Pricing	14 In Stock
-	532	25.40	6.35	45	#34-842	A\$285.10 Volume Pricing	15 In Stock
-	1064	6.35	4.00	45	#12-525	A\$238.96 Volume Pricing	13 In Stock
-	1064	12.70	6.35	45	#34-843	A\$238.96 Volume Pricing	20+ In Stock
-	1064	25.40	6.35	45	#34-845	A\$257.09 Volume Pricing	20+ In Stock
-	1064	50.80	9.53	45	#12-550	A\$723.47 Volume Pricing	8 In Stock
343 - 355	355	25.40	5.00	45	#89-450	A\$416.94 Volume Pricing	Contact Us
515 - 532	532	25.40	5.00	45	#89-451	A\$341.14 Volume Pricing	1 In Stock
1030 - 1064	1064	25.40	5.00	0	#89-452	A\$341.14 Volume Pricing	Contact Us
1030 - 1064	1064	25.40	5.00	45	#89-453	A\$341.14 Volume Pricing	Contact Us



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com