

[All Products](#) / [Optomechanics](#) / [Manual Translation Stages and Slides](#) / [Manual Stages and Slides](#)

Micro Manual Goniometers



- Small Footprint
- Zero-Backlash Drive System
- 25mm or 42mm Radius Versions Stackable to Create 2-Axis Version

Common Specifications

Physical & Mechanical Properties

Type of Movement:	Goniometer	Stage Size (mm):	66 x 19.1
Travel (°):	±10	Leadscrew Pitch (mm):	0.32
Load Capacity, Normal (kg):	0.45	Stage Size (inches):	2.6 x 0.75
Weight (g):	40		

Hardware & Interface Connectivity

Type of Drive:	Lead Screw
----------------	------------

Threading & Mounting

Mounting Threads:	(10) 0-80
-------------------	-----------

Technical Information

Products

Type	Radius R (mm)	Travel (°)	Type of Drive	Stock Number	Price	Buy
English	25	±10	Lead Screw	#13-779	A\$4,760.00	Contact Us
English	42	±10	Lead Screw	#13-780	A\$4,760.00	Contact Us



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com