

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Bandpass Filters](#)

TECHSPEC® Unmounted OD 4.0 Bandpass Filters



- Center Wavelengths from 365 to 1550nm
- 10, 25, or 50nm Full-Width Half Maximum Options
- High Transmission and Deep Blocking
- Mounted OD 4.0 [5nm](#), [10nm](#), [25nm](#) and [50nm](#) Bandpass Filters Also Available

Common Specifications

Physical & Mechanical Properties

Thickness (mm):	3.30 ±0.20	Construction:	Unmounted
Physical Durability:	Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2	Bevel:	Protective as needed

Optical Properties

Angle of Incidence (°):	0	Optical Density OD (Average):	≥4.0
Substrate:	Optical Glass	Coating:	Hard Coated
Surface Quality:	80-50		

Environmental & Durability Factors

Environmental Durability:	Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7
----------------------------------	---

Technical Information

Products

Dia. (mm)	CWL (nm)	FWHM (nm)	Minimum Transmission (%)	Blocking Wavelength Range (nm)	Stock Number	Price	Buy
12.50	365.00	10.00	≥85	200 - 1200	#15-116	A\$299.94 Volume Pricing	20+ In Stock
25.00	365.00	10.00	≥85	200 - 1200	#15-131	A\$441.66 Volume Pricing	3 In Stock
12.50	405.00	10.00	≥85	200 - 1200	#15-117	A\$273.57 Volume Pricing	3 In Stock
25.00	405.00	10.00	≥85	200 - 1200	#15-132	A\$415.30 Volume Pricing	10 In Stock
12.50	430.00	10.00	≥85	200 - 1200	#15-118	A\$273.57 Volume Pricing	1 In Stock
25.00	430.00	10.00	≥85	200 - 1200	#15-133	A\$415.30 Volume Pricing	20+ In Stock
12.50	450.00	10.00	≥85	200 - 1200	#15-119	A\$273.57 Volume Pricing	3 In Stock
25.00	450.00	10.00	≥85	200 - 1200	#15-134	A\$415.30 Volume Pricing	Contact Us
12.50	450.00	25.00	≥90	200 - 1200	#15-146	A\$273.57 Volume Pricing	20+ In Stock
25.00	450.00	25.00	≥90	200 - 1200	#15-151	A\$415.30 Volume Pricing	20+ In Stock
12.50	450.00	50.00	≥90	200 - 1200	#15-156	A\$273.57 Volume Pricing	20+ In Stock
25.00	450.00	50.00	≥90	200 - 1200	#15-164	A\$415.30 Volume Pricing	Contact Us
12.50	520.00	10.00	≥85	200 - 1200	#15-120	A\$273.57 Volume Pricing	20+ In Stock
25.00	520.00	10.00	≥85	200 - 1200	#15-135	A\$415.30 Volume Pricing	5 In Stock
12.50	525.00	25.00	≥90	200 - 1200	#15-147	A\$273.57 Volume Pricing	2 In Stock
25.00	525.00	25.00	≥90	200 - 1200	#15-152	A\$415.30 Volume Pricing	2 In Stock
12.50	525.00	50.00	≥90	200 - 1200	#15-157	A\$273.57 Volume Pricing	Contact Us

25.00	525.00	50.00	≥90	200 - 1200	#15-165	A\$415.30 Volume Pricing	20+ In Stock
12.50	532.00	10.00	≥85	200 - 1200	#15-121	A\$273.57 Volume Pricing	20+ In Stock
25.00	532.00	10.00	≥85	200 - 1200	#15-136	A\$415.30 Volume Pricing	20+ In Stock
12.50	550.00	10.00	≥85	200 - 1200	#15-122	A\$273.57 Volume Pricing	3 In Stock
25.00	550.00	10.00	≥85	200 - 1200	#15-137	A\$415.30 Volume Pricing	1 In Stock
12.50	550.00	25.00	≥90	200 - 1200	#15-148	A\$273.57 Volume Pricing	20+ In Stock
25.00	550.00	25.00	≥90	200 - 1200	#15-153	A\$415.30 Volume Pricing	2 In Stock
12.50	550.00	50.00	≥90	200 - 1200	#15-158	A\$273.57 Volume Pricing	20+ In Stock
25.00	550.00	50.00	≥90	200 - 1200	#15-166	A\$415.30 Volume Pricing	20+ In Stock
12.50	589.00	10.00	≥85	200 - 1200	#15-123	A\$273.57 Volume Pricing	20+ In Stock
25.00	589.00	10.00	≥85	200 - 1200	#15-138	A\$415.30 Volume Pricing	4 In Stock
12.50	632.00	10.00	≥85	200 - 1200	#15-124	A\$273.57 Volume Pricing	5 In Stock
25.00	632.00	10.00	≥85	200 - 1200	#15-139	A\$415.30 Volume Pricing	9 In Stock
12.50	640.00	10.00	≥85	200 - 1200	#15-125	A\$273.57 Volume Pricing	20+ In Stock
25.00	640.00	10.00	≥85	200 - 1200	#15-140	A\$415.30 Volume Pricing	1 In Stock
12.50	650.00	25.00	≥90	200 - 1200	#15-149	A\$273.57 Volume Pricing	4 In Stock
25.00	650.00	25.00	≥90	200 - 1200	#15-154	A\$415.30 Volume Pricing	2 In Stock
12.50	650.00	50.00	≥90	200 - 1200	#15-159	A\$273.57 Volume Pricing	13 In Stock
25.00	650.00	50.00	≥90	200 - 1200	#15-167	A\$415.30 Volume Pricing	2 In Stock
12.50	660.00	10.00	≥85	200 - 1200	#15-126	A\$273.57 Volume Pricing	13 In Stock

25.00	660.00	10.00	≥85	200 - 1200	#15-141	A\$415.30 Volume Pricing	1 In Stock
12.50	850.00	10.00	≥85	200 - 1200	#15-127	A\$299.94 Volume Pricing	1 In Stock
25.00	850.00	10.00	≥85	200 - 1200	#15-142	A\$441.66 Volume Pricing	1 In Stock
12.50	850.00	50.00	≥90	200 - 1200	#15-160	A\$299.94 Volume Pricing	5 In Stock
25.00	850.00	50.00	≥90	200 - 1200	#15-168	A\$441.66 Volume Pricing	14 In Stock
12.50	900.00	50.00	≥90	200 - 1200	#15-161	A\$299.94 Volume Pricing	14 In Stock
25.00	900.00	50.00	≥90	200 - 1200	#15-169	A\$441.66 Volume Pricing	20+ In Stock
12.50	905.00	10.00	≥85	200 - 1200	#15-128	A\$299.94 Volume Pricing	1 In Stock
25.00	905.00	10.00	≥85	200 - 1200	#15-143	A\$441.66 Volume Pricing	20+ In Stock
12.50	940.00	10.00	≥85	200 - 1200	#15-129	A\$299.94 Volume Pricing	1 In Stock
25.00	940.00	10.00	≥85	200 - 1200	#15-144	A\$441.66 Volume Pricing	1 In Stock
12.50	950.00	50.00	≥90	200 - 1200	#15-162	A\$299.94 Volume Pricing	2 In Stock
25.00	950.00	50.00	≥90	200 - 1200	#15-170	A\$441.66 Volume Pricing	2 In Stock
12.50	1,064.00	10.00	≥85	200 - 1200	#15-130	A\$299.94 Volume Pricing	9 In Stock
25.00	1,064.00	10.00	≥85	200 - 1200	#15-145	A\$441.66 Volume Pricing	20+ In Stock
12.50	1,550.00	25.00	≥90	200 - 1800	#15-150	A\$359.26 Volume Pricing	1 In Stock
25.00	1,550.00	25.00	≥90	200 - 1800	#15-155	A\$540.54 Volume Pricing	2 In Stock
12.50	1,550.00	50.00	≥90	200 - 1800	#15-163	A\$359.26 Volume Pricing	2 In Stock
25.00	1,550.00	50.00	≥90	200 - 1800	#15-171	A\$540.54 Volume Pricing	2 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com