

[All Products](#) / [Imaging Lenses](#) / [Zoom & Variable Magnification Lenses](#) / [Variable Magnification Lenses](#)

Computar Motorized LensConnect Variable Focal Length Lenses



- Focus, Iris, and Zoom Controlled via Simple USB Interface
- 5 MegaPixels, 1/1.8", CS-Mount or 12 MegaPixels, 1.1", C-Mount
- 4 – 10mm, 9 – 50mm, or 16 – 96mm Variable Focal Lengths Available
- [Fixed Focal Length Options](#) Available

Common Specifications

Physical & Mechanical Properties

Iris Option:	Motorized
--------------	-----------

Hardware & Interface Connectivity

Control Interface:	USB2.0 TypeA
--------------------	--------------

Length of Cable (mm):	300 ±20
-----------------------	---------

Technical Information

Products

Focal Length Range (mm)	Max. Sensor Format	Mount	WD (mm)	Aperture (f/#)	Filter Thread	Stock Number	Price	Buy
4-10	1/1.8"	CS-Mount	200 - ∞	f/1.5 - f/16	M55.0 x 0.75	#29-307	A\$1,384.00	4 In Stock
9-50	1/1.8"	CS-Mount	3000 - ∞	f/1.5 - f/16	M67.5 x 0.50	#29-308	A\$1,712.00	5 In Stock
16-96	1.1"	C-Mount	3000 - ∞	f/2.8 - f/16	M67.0 x 0.75	#24-188	A\$3,104.00	1 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com