

Tip Kit, 9 piece Conductive Silicone



Representative Picture of Straight and Bent Probes

Stock **#57-642** 7 In Stock

-

1

+

A\$88⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	A\$88.80 each
Qty 10+	A\$80.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Contents of Kit:
9 Tips: 3/8", 1/4", & 1/8" (one bent and one straight of each), 1/2" straight probe, and 3/16" and 3/32" bent probes

Regulatory Compliance	
Compliant	Reach 191:
Compliant	RoHS 2015:
View	Certificate of Conformance:

PRODUCT DETAILS

- 10" and 15" Hg Models
- ESD-Safe
- Ideal for Assembly Work with Small Optical Parts

These compact, vacuum handling tools will pick-up most of the surface mount, optical, and electrical components used in today's assemblies. The long life diaphragm vacuum pump generates six inches of mercury, and the precision pump/motor model gives more than fifteen inches for extra power. Pen Holder on side; 15" Hg series handle has auto-off feature when pen in-place. Features include: quiet operation, 5 ft of coiled static dissipative hose, set of 9 static dissipative black non-marring tips ([#57-641](#)), vacuum pick-up handle (5.25" L x 0.5" Dia), no-skid feet, and black anodized case. Additional features for 15" Hg: 12V power supply, auto on/off, variable air-flow control, ESD connection on rear, and Hand or Foot switch options for pick & place operation. 9 pc Tip (probe/cup) Kits include (cup OD size): 3/8", 1/4", and 1/8" (one each bent and straight probes), 1/2" straight probe, and 3/16" and 3/32" bent probes. [#57-641](#) contains static dissipative tips, and [#57-642](#) contains ESD-Safe (Conductive) tips.