

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Longpass Filters](#)

Hoya Colored Glass Longpass Filters

See More by [Hoya](#)



- UV, VIS and IR Pass Ranges
- VIS Can Be Used for Color Bandpass
- Also Available [Mounted](#)

Common Specifications


Physical & Mechanical Properties

Bevel:	Protective as needed
--------	----------------------


Optical Properties

Substrate:	Colored Glass
Coating:	Uncoated

Technical Information



Hoya Colored Glass Longpass Filters



Products

Dimensions (mm)	Dia. (mm)	Glass/Filter Number	Cut-On Wavelength (nm)	Thickness (mm)	Stock Number	Price	Buy
-	12.50	Hoya UV28N	280.00	1.00	#18-791	A\$54.38 Volume Pricing	20+ In Stock
-	12.50	Hoya UV28N	280.00	2.50	#18-792	A\$54.38 Volume Pricing	20+ In Stock
-	25.40	Hoya UV28N	280.00	1.00	#18-793	A\$75.81 Volume Pricing	11 In Stock
-	25.40	Hoya UV28N	280.00	2.50	#18-794	A\$75.81 Volume Pricing	20+ In Stock
-	50.00	Hoya UV28N	280.00	1.00	#18-795	A\$151.62 Volume Pricing	7 In Stock
-	50.00	Hoya UV28N	280.00	2.50	#18-796	A\$151.62 Volume Pricing	7 In Stock
50.8 x 50.8	-	Hoya UV28N	280.00	1.00	#18-797	A\$151.62 Volume Pricing	5 In Stock
50.8 x 50.8	-	Hoya UV28N	280.00	2.50	#18-798	A\$151.62 Volume Pricing	2 In Stock
-	12.50	Hoya UV30N	300.00	1.00	#18-799	A\$54.38 Volume Pricing	20+ In Stock
-	12.50	Hoya UV30N	300.00	2.50	#18-800	A\$54.38 Volume Pricing	20+ In Stock
-	25.40	Hoya UV30N	300.00	1.00	#18-801	A\$75.81 Volume Pricing	20+ In Stock
-	25.40	Hoya UV30N	300.00	2.50	#18-802	A\$75.81 Volume Pricing	20+ In Stock
-	50.00	Hoya UV30N	300.00	1.00	#18-803	A\$151.62 Volume Pricing	2 In Stock
-	50.00	Hoya UV30N	300.00	2.50	#18-804	A\$151.62 Volume Pricing	9 In Stock
50.8 x 50.8	-	Hoya UV30N	300.00	1.00	#18-805	A\$151.62 Volume Pricing	4 In Stock
50.8 x 50.8	-	Hoya UV30N	300.00	2.50	#18-806	A\$151.62 Volume Pricing	5 In Stock
-	12.50	Hoya UV32N	320.00	1.00	#18-807	A\$54.38 Volume Pricing	20+ In Stock
-	12.50	Hoya UV32N	320.00	2.50	#18-808	A\$54.38 Volume Pricing	20+ In Stock

-	25.40	Hoya UV32N	320.00	1.00	#18-809	A\$75.81 Volume Pricing	20+ In Stock
-	25.40	Hoya UV32N	320.00	2.50	#18-810	A\$75.81 Volume Pricing	20+ In Stock
-	50.00	Hoya UV32N	320.00	1.00	#18-811	A\$151.62 Volume Pricing	8 In Stock
-	50.00	Hoya UV32N	320.00	2.50	#18-812	A\$151.62 Volume Pricing	7 In Stock
50.8 x 50.8	-	Hoya UV32N	320.00	1.00	#18-813	A\$151.62 Volume Pricing	6 In Stock
50.8 x 50.8	-	Hoya UV32N	320.00	2.50	#18-814	A\$151.62 Volume Pricing	7 In Stock
-	12.50	Hoya UV34N	340.00	1.00	#18-815	A\$54.38 Volume Pricing	20+ In Stock
-	12.50	Hoya UV34N	340.00	2.50	#18-816	A\$54.38 Volume Pricing	20+ In Stock
-	25.40	Hoya UV34N	340.00	1.00	#18-817	A\$75.81 Volume Pricing	20+ In Stock
-	25.40	Hoya UV34N	340.00	2.50	#18-818	A\$75.81 Volume Pricing	20+ In Stock
-	50.00	Hoya UV34N	340.00	1.00	#18-819	A\$151.62 Volume Pricing	5 In Stock
-	50.00	Hoya UV34N	340.00	2.50	#18-820	A\$151.62 Volume Pricing	Contact Us
50.8 x 50.8	-	Hoya UV34N	340.00	1.00	#18-821	A\$151.62 Volume Pricing	6 In Stock
50.8 x 50.8	-	Hoya UV34N	340.00	2.50	#18-822	A\$151.62 Volume Pricing	2 In Stock
-	12.50	Hoya UV36N	360.00	1.00	#18-823	A\$54.38 Volume Pricing	20+ In Stock
-	12.50	Hoya UV36N	360.00	2.50	#18-824	A\$54.38 Volume Pricing	20+ In Stock
-	25.40	Hoya UV36N	360.00	1.00	#18-825	A\$75.81 Volume Pricing	20+ In Stock
-	25.40	Hoya UV36N	360.00	2.50	#18-826	A\$75.81 Volume Pricing	16 In Stock
-	50.00	Hoya UV36N	360.00	1.00	#18-827	A\$151.62 Volume Pricing	Contact Us
-	50.00	Hoya UV36N	360.00	2.50	#18-828	A\$151.62 Volume Pricing	1 In Stock
50.8 x 50.8	-	Hoya UV36N	360.00	1.00	#18-829	A\$151.62 Volume Pricing	4 In Stock

50.8 x 50.8	-	Hoya UV36N	360.00	2.50	#18-830	A\$151.62 Volume Pricing	7 In Stock
-	12.50	Hoya L37	370.00	2.50	#66-038	A\$54.38 Volume Pricing	20+ In Stock
-	25.40	Hoya L37	370.00	2.50	#66-049	A\$75.81 Volume Pricing	6 In Stock
50.8 x 50.8	-	Hoya L37	370.00	2.50	#66-060	A\$151.62 Volume Pricing	14 In Stock
-	50.00	Hoya L37	370.00	2.50	#66-075	A\$151.62 Volume Pricing	8 In Stock
#66-076 Clearance							
 Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
-	50.00	Hoya L38	380.00	2.50		A\$49.36	13 In Stock
-	12.50	Hoya L38	380.00	1.00	#18-831	A\$54.38 Volume Pricing	12 In Stock
-	12.50	Hoya L38	380.00	2.50	#18-832	A\$54.38 Volume Pricing	20+ In Stock
-	25.40	Hoya L38	380.00	1.00	#18-833	A\$75.81 Volume Pricing	20+ In Stock
-	25.40	Hoya L38	380.00	2.50	#18-834	A\$75.81 Volume Pricing	13 In Stock
-	50.00	Hoya L38	380.00	1.00	#18-835	A\$151.62 Volume Pricing	10 In Stock
-	50.00	Hoya L38	380.00	2.50	#18-836	A\$151.62 Volume Pricing	1 In Stock
50.8 x 50.8	-	Hoya L38	380.00	1.00	#18-837	A\$151.62 Volume Pricing	8 In Stock
50.8 x 50.8	-	Hoya L38	380.00	2.50	#18-838	A\$151.62 Volume Pricing	7 In Stock
-	12.50	Hoya L39	390.00	1.00	#18-839	A\$54.38 Volume Pricing	20+ In Stock

-	12.50	Hoya L39	390.00	2.50	#18-840	A\$54.38 Volume Pricing	20+ In Stock
-	25.40	Hoya L39	390.00	1.00	#18-841	A\$75.81 Volume Pricing	20+ In Stock
-	25.40	Hoya L39	390.00	2.50	#18-842	A\$75.81 Volume Pricing	20+ In Stock
-	50.00	Hoya L39	390.00	1.00	#18-843	A\$151.62 Volume Pricing	5 In Stock
-	50.00	Hoya L39	390.00	2.50	#18-844	A\$151.62 Volume Pricing	9 In Stock
50.8 x 50.8	-	Hoya L39	390.00	1.00	#18-845	A\$151.62 Volume Pricing	11 In Stock
50.8 x 50.8	-	Hoya L39	390.00	2.50	#18-846	A\$151.62 Volume Pricing	2 In Stock
-	12.50	Hoya L42	420.00	1.00	#18-847	A\$54.38 Volume Pricing	20+ In Stock
-	12.50	Hoya L42	420.00	2.50	#18-848	A\$54.38 Volume Pricing	20+ In Stock
-	25.40	Hoya L42	420.00	1.00	#18-849	A\$75.81 Volume Pricing	20+ In Stock
-	25.40	Hoya L42	420.00	2.50	#18-850	A\$75.81 Volume Pricing	9 In Stock
-	50.00	Hoya L42	420.00	1.00	#18-851	A\$151.62 Volume Pricing	6 In Stock
-	50.00	Hoya L42	420.00	2.50	#18-852	A\$151.62 Volume Pricing	8 In Stock
50.8 x 50.8	-	Hoya L42	420.00	1.00	#18-853	A\$151.62 Volume Pricing	2 In Stock
50.8 x 50.8	-	Hoya L42	420.00	2.50	#18-854	A\$151.62 Volume Pricing	8 In Stock
-	12.50	Hoya Y44	440.00	1.00	#18-855	A\$54.38 Volume Pricing	20+ In Stock
-	12.50	Hoya Y44	440.00	2.50	#18-856	A\$54.38 Volume Pricing	20+ In Stock
-	25.40	Hoya Y44	440.00	1.00	#18-857	A\$75.81 Volume Pricing	20+ In Stock
-	25.40	Hoya Y44	440.00	2.50	#18-858	A\$75.81 Volume Pricing	15 In Stock
-	50.00	Hoya Y44	440.00	1.00	#18-859	A\$151.62 Volume Pricing	7 In Stock
-	50.00	Hoya Y44	440.00	2.50	#18-860	A\$151.62 Volume Pricing	9 In Stock
50.8 x 50.8	-	Hoya Y44	440.00	1.00	#18-861	A\$151.62 Volume Pricing	5 In Stock
50.8 x 50.8	-	Hoya Y44	440.00	2.50	#18-862	A\$151.62 Volume Pricing	1 In Stock

-	12.50	Hoya Y48	480.00	1.00	#18-863	A\$54.38 Volume Pricing	20+ In Stock
-	12.50	Hoya Y48	480.00	2.50	#18-864	A\$54.38 Volume Pricing	20+ In Stock
-	25.40	Hoya Y48	480.00	1.00	#18-865	A\$75.81 Volume Pricing	8 In Stock
-	25.40	Hoya Y48	480.00	2.50	#18-866	A\$75.81 Volume Pricing	20+ In Stock
-	50.00	Hoya Y48	480.00	1.00	#18-867	A\$151.62 Volume Pricing	5 In Stock
-	50.00	Hoya Y48	480.00	2.50	#18-868	A\$151.62 Volume Pricing	8 In Stock
50.8 x 50.8	-	Hoya Y48	480.00	1.00	#18-869	A\$151.62 Volume Pricing	1 In Stock
50.8 x 50.8	-	Hoya Y48	480.00	2.50	#18-870	A\$151.62 Volume Pricing	2 In Stock
-	12.50	Hoya Y50	500.00	2.50	#66-039	A\$54.38 Volume Pricing	4 In Stock
-	25.40	Hoya Y50	500.00	2.50	#66-050	A\$75.81 Volume Pricing	20+ In Stock
50.8 x 50.8	-	Hoya Y50	500.00	2.50	#66-061	A\$151.62 Volume Pricing	20+ In Stock
-	50.00	Hoya Y50	500.00	2.50	#66-084	A\$151.62 Volume Pricing	15 In Stock
-	12.50	Hoya Y52	520.00	1.00	#18-871	A\$54.38 Volume Pricing	9 In Stock
-	12.50	Hoya Y52	520.00	2.50	#18-872	A\$54.38 Volume Pricing	20+ In Stock
-	25.40	Hoya Y52	520.00	1.00	#18-873	A\$75.81 Volume Pricing	5 In Stock
-	25.40	Hoya Y52	520.00	2.50	#18-874	A\$75.81 Volume Pricing	3 In Stock
-	50.00	Hoya Y52	520.00	1.00	#18-875	A\$151.62 Volume Pricing	7 In Stock
-	50.00	Hoya Y52	520.00	2.50	#18-876	A\$151.62 Volume Pricing	2 In Stock
50.8 x 50.8	-	Hoya Y52	520.00	1.00	#18-877	A\$151.62 Volume Pricing	4 In Stock
50.8 x 50.8	-	Hoya Y52	520.00	2.50	#18-878	A\$151.62 Volume Pricing	9 In Stock
-	12.50	Hoya O54	540.00	2.50	#66-040	A\$54.38 Volume Pricing	20+ In Stock
-	25.40	Hoya O54	540.00	2.50	#66-051	A\$75.81 Volume Pricing	20+ In Stock

50.8 x 50.8	-	Hoya O54	540.00	2.50	#66-062	A\$151.62 Volume Pricing	20+ In Stock
-	50.00	Hoya O54	540.00	2.50	#66-087	A\$151.62 Volume Pricing	15 In Stock
-	12.50	Hoya O56	560.00	2.50	#66-041	A\$54.38 Volume Pricing	Contact Us
-	25.40	Hoya O56	560.00	2.50	#66-052	A\$75.81 Volume Pricing	20+ In Stock
50.8 x 50.8	-	Hoya O56	560.00	2.50	#66-063	A\$151.62 Volume Pricing	20+ In Stock
-	50.00	Hoya O56	560.00	2.50	#66-089	A\$151.62 Volume Pricing	20+ In Stock
-	12.50	Hoya O58	580.00	2.50	#66-042	A\$54.38 Volume Pricing	20+ In Stock
-	25.40	Hoya O58	580.00	2.50	#66-053	A\$75.81 Volume Pricing	20+ In Stock
-	50.00	Hoya O58	580.00	2.50	#66-091	A\$151.62 Volume Pricing	20+ In Stock
-	12.50	Hoya R60	600.00	2.50	#66-043	A\$54.38 Volume Pricing	20+ In Stock
-	25.40	Hoya R60	600.00	2.50	#66-054	A\$75.81 Volume Pricing	20+ In Stock
50.8 x 50.8	-	Hoya R60	600.00	2.50	#66-065	A\$151.62 Volume Pricing	20+ In Stock
-	50.00	Hoya R60	600.00	2.50	#66-093	A\$151.62 Volume Pricing	14 In Stock
-	12.50	Hoya R62	620.00	2.50	#66-044	A\$54.38 Volume Pricing	20+ In Stock
-	25.40	Hoya R62	620.00	2.50	#66-055	A\$75.81 Volume Pricing	10 In Stock
50.8 x 50.8	-	Hoya R62	620.00	2.50	#66-066	A\$151.62 Volume Pricing	20+ In Stock
-	50.00	Hoya R62	620.00	2.50	#66-095	A\$151.62 Volume Pricing	20+ In Stock
-	12.50	Hoya R64	640.00	1.00	#18-879	A\$54.38 Volume Pricing	17 In Stock
-	12.50	Hoya R64	640.00	2.50	#18-880	A\$54.38 Volume Pricing	8 In Stock
-	25.40	Hoya R64	640.00	1.00	#18-881	A\$75.81 Volume Pricing	20+ In Stock
-	25.40	Hoya R64	640.00	2.50	#18-882	A\$75.81 Volume Pricing	20+ In Stock
-	50.00	Hoya R64	640.00	1.00	#18-883	A\$151.62 Volume Pricing	7 In Stock

-	50.00	Hoya R64	640.00	2.50	#18-884	A\$151.62 Volume Pricing	11 In Stock
50.8 x 50.8	-	Hoya R64	640.00	1.00	#18-885	A\$151.62 Volume Pricing	9 In Stock
50.8 x 50.8	-	Hoya R64	640.00	2.50	#18-886	A\$151.62 Volume Pricing	5 In Stock
-	12.50	Hoya R66	660.00	2.50	#66-045	A\$54.38 Volume Pricing	20+ In Stock
-	25.40	Hoya R66	660.00	2.50	#66-056	A\$75.81 Volume Pricing	20+ In Stock
50.8 x 50.8	-	Hoya R66	660.00	2.50	#66-067	A\$151.62 Volume Pricing	3 In Stock
-	50.00	Hoya R66	660.00	2.50	#66-098	A\$151.62 Volume Pricing	10 In Stock
-	12.50	Hoya R70	700.00	1.00	#18-887	A\$54.38 Volume Pricing	20+ In Stock
-	12.50	Hoya R70	700.00	2.50	#18-888	A\$54.38 Volume Pricing	20+ In Stock
-	25.40	Hoya R70	700.00	1.00	#18-889	A\$75.81 Volume Pricing	20+ In Stock
-	25.40	Hoya R70	700.00	2.50	#18-890	A\$75.81 Volume Pricing	14 In Stock
-	50.00	Hoya R70	700.00	1.00	#18-891	A\$151.62 Volume Pricing	4 In Stock
-	50.00	Hoya R70	700.00	2.50	#18-892	A\$151.62 Volume Pricing	5 In Stock
50.8 x 50.8	-	Hoya R70	700.00	1.00	#18-893	A\$151.62 Volume Pricing	5 In Stock
50.8 x 50.8	-	Hoya R70	700.00	2.50	#18-894	A\$151.62 Volume Pricing	7 In Stock
-	12.50	Hoya R72	720.00	2.50	#66-046	A\$54.38 Volume Pricing	20+ In Stock
-	25.40	Hoya R72	720.00	2.50	#66-057	A\$75.81 Volume Pricing	11 In Stock
50.8 x 50.8	-	Hoya R72	720.00	2.50	#66-068	A\$151.62 Volume Pricing	20+ In Stock
-	50.00	Hoya R72	720.00	2.50	#66-102	A\$151.62 Volume Pricing	13 In Stock
-	12.50	Hoya IR76N	760.00	2.50	#66-047	A\$54.38 Volume Pricing	2 In Stock
-	25.40	Hoya IR76N	760.00	2.50	#66-058	A\$75.81 Volume Pricing	20+ In Stock
50.8 x 50.8	-	Hoya IR76N	760.00	2.50	#66-069	A\$151.62 Volume Pricing	20+ In Stock
-	50.00	Hoya IR76N	760.00	2.50	#66-103	A\$151.62 Volume Pricing	14 In Stock

-	12.50	Hoya IR80N	800.00	2.50	#66-048	A\$54.38 Volume Pricing	17 In Stock
-	25.40	Hoya IR80N	800.00	2.50	#66-059	A\$75.81 Volume Pricing	20+ In Stock
50.8 x 50.8	-	Hoya IR80N	800.00	2.50	#66-070	A\$151.62 Volume Pricing	20+ In Stock
-	50.00	Hoya IR80N	800.00	2.50	#66-105	A\$151.62 Volume Pricing	20+ In Stock
-	12.50	Hoya IR83N	830.00	1.00	#18-895	A\$54.38 Volume Pricing	20+ In Stock
-	12.50	Hoya IR83N	830.00	2.50	#18-896	A\$54.38 Volume Pricing	20+ In Stock
-	25.40	Hoya IR83N	830.00	1.00	#18-897	A\$75.81 Volume Pricing	14 In Stock
-	25.40	Hoya IR83N	830.00	2.50	#18-898	A\$75.81 Volume Pricing	5 In Stock
-	50.00	Hoya IR83N	830.00	1.00	#18-899	A\$151.62 Volume Pricing	6 In Stock
-	50.00	Hoya IR83N	830.00	2.50	#18-900	A\$151.62 Volume Pricing	1 In Stock
50.8 x 50.8	-	Hoya IR83N	830.00	1.00	#18-901	A\$151.62 Volume Pricing	4 In Stock
50.8 x 50.8	-	Hoya IR83N	830.00	2.50	#18-902	A\$151.62 Volume Pricing	8 In Stock
-	12.50	Hoya IR85N	850.00	1.00	#18-903	A\$54.38 Volume Pricing	13 In Stock
-	12.50	Hoya IR85N	850.00	2.50	#18-904	A\$54.38 Volume Pricing	20+ In Stock
-	25.40	Hoya IR85N	850.00	1.00	#18-905	A\$75.81 Volume Pricing	14 In Stock
-	25.40	Hoya IR85N	850.00	2.50	#18-906	A\$75.81 Volume Pricing	12 In Stock
-	50.00	Hoya IR85N	850.00	1.00	#18-907	A\$151.62 Volume Pricing	2 In Stock
-	50.00	Hoya IR85N	850.00	2.50	#18-908	A\$151.62 Volume Pricing	7 In Stock
50.8 x 50.8	-	Hoya IR85N	850.00	1.00	#18-909	A\$151.62 Volume Pricing	7 In Stock
50.8 x 50.8	-	Hoya IR85N	850.00	2.50	#18-910	A\$151.62 Volume Pricing	4 In Stock
-	12.50	Hoya RM100	1,000.00	1.00	#18-911	A\$54.38 Volume Pricing	20+ In Stock
-	12.50	Hoya RM100	1,000.00	2.50	#18-912	A\$54.38 Volume Pricing	20+ In Stock

-	25.40	Hoya RM100	1,000.00	1.00	#18-913	A\$75.81 Volume Pricing	20+ In Stock
-	25.40	Hoya RM100	1,000.00	2.50	#18-914	A\$75.81 Volume Pricing	20+ In Stock
-	50.00	Hoya RM100	1,000.00	1.00	#18-915	A\$151.62 Volume Pricing	8 In Stock
-	50.00	Hoya RM100	1,000.00	2.50	#18-916	A\$151.62 Volume Pricing	2 In Stock
50.8 x 50.8	-	Hoya RM100	1,000.00	1.00	#18-917	A\$151.62 Volume Pricing	5 In Stock
		Edmund optics worldwide	1,000.00	2.50	#18-918	A\$151.62 Volume Pricing	1 In Stock