


[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Light Pipes and Homogenizing Rods](#)

TECHSPEC® N-BK7 Light Pipe Homogenizing Rods



- Homogenizes Non-Uniform Light Sources
- Hexagonal Entrance Aperture
- Uncoated and VIS-EXT Coated Options Available
- Ideal for OEM Illumination
- Additional [Light Pipe Homogenizing Rods](#) Available

Common Specifications

Physical & Mechanical Properties

Parallelism (arcmin):	<5.00
-----------------------	-------

Optical Properties


Substrate:	N-BK7
------------	-----------------------

Surface Quality:	60-40
------------------	-------

Aperture Tolerance (mm):	±0.10
--------------------------	-------

Image Orientation:	Light Homogenization
--------------------	----------------------

Technical Information



Products

Entrance and Exit Aperture (mm)	Wavelength Range (nm)	Length (mm)	Stock Number	Price	Buy
2.00	350 - 2200	25.00	#48-582	A\$219.18 Volume Pricing	20+ In Stock
2.00	350 - 2200	50.00	#63-080	A\$227.42 Volume Pricing	20+ In Stock
2.00	350 - 2200	75.00	#63-081	A\$273.57 Volume Pricing	17 In Stock
4.00	350 - 2200	25.00	#63-082	A\$171.39 Volume Pricing	Contact Us
4.00	350 - 2200	50.00	#49-402	A\$192.82 Volume Pricing	20+ In Stock
4.00	350 - 2200	100.00	#63-083	A\$227.42 Volume Pricing	17 In Stock
5.00	350 - 2200	30.00	#63-084	A\$184.58 Volume Pricing	20+ In Stock
5.00	350 - 2200	60.00	#48-583	A\$206.00 Volume Pricing	20+ In Stock
5.00	350 - 2200	120.00	#63-085	A\$248.85 Volume Pricing	20+ In Stock
6.00	350 - 2200	50.00	#63-086	A\$192.82 Volume Pricing	20+ In Stock
6.00	350 - 2200	75.00	#49-403	A\$219.18 Volume Pricing	20+ In Stock
6.00	350 - 2200	150.00	#63-087	A\$262.03 Volume Pricing	15 In Stock
8.00	350 - 2200	50.00	#63-088	A\$219.18 Volume Pricing	20+ In Stock
8.00	350 - 2200	100.00	#49-404	A\$240.61 Volume Pricing	17 In Stock
10.00	350 - 2200	75.00	#63-090	A\$248.85 Volume Pricing	20+ In Stock
10.00	350 - 2200	125.00	#48-584	A\$273.57 Volume Pricing	20+ In Stock
10.00	350 - 2200	175.00	#63-091	A\$294.99 Volume Pricing	Contact Us

12.5	350 - 2200	75.00	#84-529	A\$262.03 Volume Pricing	20+ In Stock
12.5	350 - 2200	150.00	#84-530	A\$286.75 Volume Pricing	14 In Stock
12.5	350 - 2200	250.00	#84-531	A\$342.78 Volume Pricing	5 In Stock
15.0	350 - 2200	100.00	#84-532	A\$321.36 Volume Pricing	20+ In Stock
15.0	350 - 2200	300.00	#84-534	A\$436.72 Volume Pricing	6 In Stock
20.0	350 - 2200	200.00	#84-536	A\$436.72 Volume Pricing	20+ In Stock
20.0	350 - 2200	125.00	#84-535	A\$372.45 Volume Pricing	20+ In Stock
20.0	350 - 2200	300.00	#84-537	A\$557.02 Volume Pricing	20+ In Stock
2.00	350 - 700	25.00	#72-725	A\$286.75 Volume Pricing	5 In Stock
2.00	350 - 700	50.00	#72-726	A\$294.99 Volume Pricing	5 In Stock
2.00	350 - 700	75.00	#72-727	A\$342.78 Volume Pricing	Contact Us
4.00	350 - 700	25.00	#72-728	A\$240.61 Volume Pricing	4 In Stock
4.00	350 - 700	50.00	#72-729	A\$262.03 Volume Pricing	5 In Stock
4.00	350 - 700	100.00	#72-730	A\$294.99 Volume Pricing	2 In Stock
5.00	350 - 700	30.00	#72-731	A\$252.14 Volume Pricing	5 In Stock
5.00	350 - 700	60.00	#72-732	A\$273.57 Volume Pricing	2 In Stock
5.00	350 - 700	120.00	#72-733	A\$316.42 Volume Pricing	2 In Stock
6.00	350 - 700	50.00	#72-734	A\$262.03 Volume Pricing	4 In Stock
6.00	350 - 700	75.00	#72-735	A\$286.75 Volume Pricing	3 In Stock
6.00	350 - 700	150.00	#72-736	A\$329.60 Volume Pricing	2 In Stock

8.00	350 - 700	50.00	#72-737	A\$294.99 Volume Pricing	3 In Stock
8.00	350 - 700	100.00	#72-738	A\$316.42 Volume Pricing	1 In Stock
10.00	350 - 700	75.00	#72-739	A\$326.30 Volume Pricing	3 In Stock
10.00	350 - 700	125.00	#72-740	A\$351.02 Volume Pricing	5 In Stock
10.00	350 - 700	175.00	#72-741	A\$372.45 Volume Pricing	2 In Stock
12.50	350 - 700	75.00	#72-742	A\$337.84 Volume Pricing	2 In Stock
12.50	350 - 700	150.00	#72-743	A\$364.21 Volume Pricing	2 In Stock
12.50	350 - 700	250.00	#72-744	A\$420.24 Volume Pricing	5 In Stock
15.00	350 - 700	100.00	#72-745	A\$407.06 Volume Pricing	Contact Us
15.00	350 - 700	300.00	#72-746	A\$522.42 Volume Pricing	Contact Us
20.00	350 - 700	200.00	#72-747	A\$530.66 Volume Pricing	5 In Stock
20.00	350 - 700	125.00	#72-748	A\$466.38 Volume Pricing	1 In Stock
20.00	350 - 700	300.00	#72-749	A\$650.96 Volume Pricing	Contact Us



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com