


[All Products](#) / [Optics](#) / [Polarization Optics](#) / [Linear Polarizers](#) / [Wire Grid \(Reflective\) Polarizers](#)

TECHSPEC®

Wire Grid Polarizing Film



- High Contrast, Reflective Design
- Excellent Visible and NIR Performance
- Superior Durability Under High Temperatures and Humidity

Common Specifications


Physical & Mechanical Properties

Construction:	Wire Grid
---------------	-----------



Optical Properties

Angle of Incidence (°):	0 - 45
Wavelength Range (nm):	400 - 1200

Technical Information



Products

Operating Temperature (°C)	Substrate	Thickness (mm)	Dimensions (mm)	Dia. (mm)	Extinction Ratio	Stock Number	Price	Buy
#70-546 Clearance								
60 Max @ 90% RH 105 in dry conditions	Aluminium Wires on COP	0.19	12.50 x 12.50	-	2000:1 Avg		A\$84.05 Volume Pricing	14 In Stock
						Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.		
#70-547 Clearance								
60 Max @ 90% RH 105 in dry conditions	Aluminium Wires on COP	0.19	20.00 x 20.00	-	2000:1 Avg		A\$105.47 Volume Pricing	Contact Us
						Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.		

[#70-552 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

60 Max @
90% RH 105
in dry
conditions

Aluminium
Wires on
COP

0.19

75.00 x 75.00

-

2000:1 Avg

A\$466.38
[Volume Pricing](#)

Contact Us

[#20-232 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

60 Max @
90% RH
105 in dry
conditions

[Aluminium
Wires on
COP](#)

0.19

12.5 x 12.5

-

>1415:1

A\$57.60

Contact Us

[#20-234 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

60 Max @ 90% RH 105 in dry conditions	Aluminium Wires on COP	0.19	-	25.00	>1415:1	A\$77.37	1 In Stock
--	--	------	---	-------	---------	----------	------------

[#20-235 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

60 Max @ 90% RH 105 in dry conditions	Aluminium Wires on COP	0.19	25 x 25	-	>1415:1	A\$92.21	Contact Us
--	--	------	---------	---	---------	----------	------------

[#20-237 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Reserve up to 80% off select products.

60 Max @
90% RH
105 in dry
conditions

[Aluminium](#)
[Wires on](#)
[COP](#)

0.19 50 x 50 - >1415:1

A\$230.64

5 In Stock



Edmund
optics | worldwide

Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com

