

[All Products](#) / [Laser Optics](#) / [Laser Beam Expanders](#) / [Vega® Beam Expanders](#)

TECHSPEC®

Vega® Broadband Beam Expanders



- AR Coated for Broadband Tunable Laser Sources
- Fixed Magnifications Available from 1.5X to 20X
- Divergence Adjustable through Rotating Optical Design

Common Specifications

Optical Properties

Angle of Incidence (°):	0	Design Wavelength DWL (nm):	Broadband
Divergence Adjustment:	Rotating Optics		

Technical Information

Products

Wavelength Range (nm)	Expansion Power	Entrance Aperture (mm)	Exit Aperture (mm)	Substrate	Stock Number	Price	Buy
250 - 532	1.5X	8	23	Fused Silica	#12-876	A\$758.08 Volume Pricing	2 In Stock
250 - 532	2X	8	23	Fused Silica	#39-725	A\$758.08 Volume Pricing	2 In Stock
250 - 532	3X	8	23	Fused Silica	#39-726	A\$758.08 Volume Pricing	3 In Stock
250 - 532	4X	7.5	26	Fused Silica	#19-405	A\$758.08	1 In Stock
250 - 532	5X	7.1	25.5	Fused Silica	#39-727	A\$964.08 Volume Pricing	4 In Stock
250 - 532	7X	7.1	25.5	Fused Silica	#39-732	A\$964.08 Volume Pricing	4 In Stock
250 - 532	10X	5.45	25.5	Fused Silica	#39-733	A\$964.08 Volume Pricing	1 In Stock
250 - 532	20X	4.5	31.5	Fused Silica	#39-734	A\$1,491.44 Volume Pricing	14 In Stock
500 - 1090	1.5X	8	23	Fused Silica	#12-877	A\$708.64 Volume Pricing	3 In Stock
500 - 1090	2X	8	23	Fused Silica	#39-736	A\$708.64 Volume Pricing	5 In Stock
500 - 1090	3X	8	23	Fused Silica	#39-737	A\$708.64 Volume Pricing	7 In Stock
500 - 1090	4X	7.5	26	Fused Silica	#19-406	A\$708.64	1 In Stock
500 - 1090	5X	7.1	25.5	Fused Silica	#39-738	A\$898.16 Volume Pricing	5 In Stock
500 - 1090	7X	7.1	25.5	Fused Silica	#39-739	A\$898.16 Volume Pricing	1 In Stock
500 - 1090	10X	5.45	25.5	Fused Silica	#39-740	A\$898.16 Volume Pricing	2 In Stock
500 - 1090	20X	4.5	31.5	Fused Silica	#39-741	A\$1,450.24 Volume Pricing	3 In Stock
1030 - 1550	1.5X	8	23	Fused Silica	#12-878	A\$708.64 Volume Pricing	3 In Stock

1030 - 1550	2X	8	23	Fused Silica	#39-742	A\$708.64 Volume Pricing	3 In Stock
1030 - 1550	3X	8	23	Fused Silica	#39-743	A\$708.64 Volume Pricing	5 In Stock
1030 - 1550	4X	7.5	26	Fused Silica	#19-407	A\$708.64	3 In Stock
1030 - 1550	5X	7.1	25.5	Fused Silica	#39-744	A\$898.16 Volume Pricing	3 In Stock
1030 - 1550	7X	7.1	25.5	Fused Silica	#39-745	A\$898.16 Volume Pricing	2 In Stock
1030 - 1550	10X	5.45	25.5	Fused Silica	#39-746	A\$898.16 Volume Pricing	3 In Stock
1030 - 1550	20X	4.5	31.5	Fused Silica	#39-747	A\$1,450.24 Volume Pricing	Contact Us
1900 - 2100	2X	10	23	Fused Silica	#37-357	A\$1,252.48 Volume Pricing	1 In Stock
1900 - 2100	3X	10	23	Fused Silica	#37-341	A\$1,252.48 Volume Pricing	2 In Stock
1900 - 2100	2X	10	23	Fused Silica	#37-376	A\$1,046.48 Volume Pricing	3 In Stock
1900 - 2100	3X	10	23	Fused Silica	#37-377	A\$1,046.48 Volume Pricing	2 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com