


[All Products](#) /
 [Optics](#) /
 [Optical Lenses](#) /
 [Plano-Convex \(PCX\) Lenses](#) /
 [UV and IR Plano-Convex \(PCX\) Lenses](#)

ISP Optics Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses

See More by [ISP Optics](#)



- Low Dispersion and Absorption from 0.6 – 18μm
- High Resistance to Thermal Shock
- Uncoated or BBAR Coated for 8 – 12μm

Common Specifications

Physical & Mechanical Properties

Bevel:	Protective as needed	Centering (arcmin):	<3
---------------	----------------------	----------------------------	----

Optical Properties

Substrate:	Zinc Selenide (ZnSe), CVD Grade	Focal Length Tolerance (%):	±2
Surface Quality:	60-40	Irregularity (P-V) @ 10.6μm:	λ/20

Technical Information

Products

Dia. (mm)	EFL (mm)	BFL (mm)	Coating	Model Number	Stock Number	Price	Buy
#24-947 Clearance							
							
Clearance							
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
25.40	200.00	199.52	Uncoated	ZC-PX-25-200		A\$572.72	1 In Stock
#24-952 Clearance							
							
Clearance							
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
38.10	75.00	74.14	Uncoated	ZC-PX-38-76		A\$478.32	6 In Stock

[#24-953 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

38.10 100.00 98.41 Uncoated ZC-PX-38-100

A\$478.32

3 In Stock

[#24-956 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

38.10 200.00 199.39 Uncoated ZC-PX-38-200

A\$478.32

5 In Stock

[#24-961 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

50.80 100.00 97.78 Uncoated ZC-PX-50-100

A\$780.72

3 In Stock

[#24-982 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

12.70 25.40 24.56 BBAR (8000-12000nm) AR812-ZC-PX-12-25

A\$198.32

14 In Stock

[#24-992 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

25.40	500.00	496.87	BBAR (8000- 12000nm)	AR812- ZC-PX- 25-500	A\$332.72	1 In Stock
-------	--------	--------	----------------------------	----------------------------	-----------	------------

[#24-994 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

38.10	63.50	61.84	BBAR (8000- 12000nm)	AR812- ZC-PX- 38-63	A\$534.32	3 In Stock
-------	-------	-------	----------------------------	---------------------------	-----------	------------

[#24-999 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

38.10	200.00	199.39	BBAR (8000-12000nm)	AR812-ZC-PX-38-200	A\$534.32	2 In Stock
-------	--------	--------	---------------------	--------------------	-----------	------------



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com