

[All Products](#) / [Lab and Production](#) / [UV Lamps and Accessories](#)

Solid State UV Flood Light Systems



- Large, Uniform UV Light Output
- 380nm Center Wavelength
- Up to 0.8W/cm² UV Irradiance

Common Specifications

General

Operating Lifetime (hours): >20,000

Physical & Mechanical Properties

Dimensions (mm): UV Curing Head: 55 x 52 x 148
Control Box: 160 x 150 x 80

Optical Properties

Wavelength (nm):	380.00 ±5	Beam Size (mm):	50 x 50mm (30mm WD) 100 x 100mm (100mm WD)
------------------	-----------	-----------------	---

Working Distance (mm):	30 - 100	Irradiance (W/cm ²):	0.8
------------------------	----------	----------------------------------	-----

Hardware & Interface Connectivity

Power Requirement: AC 100 - 240V

Technical Information

Products

Title	Stock Number	Price	Buy
Solid State UV Flood Light Systems	#16-762	A\$5,016.00	2 In Stock

[#16-762-RCD-05P Recertified](#)



Recertified

Stock No.: 16-762-RCD-05P
Recertified Code: 05P (All Original Parts
Included, Perfect)

Recertified
Products

Typically 1-2 Recertified Products are in stock at a time. Please contact our sales team if you would like exact availability of an item.

Recertified products are those identified with the recertified logo indicating they were returned to Edmund Optics® and cannot be sold as new for the following reasons:

- Open Box – Missing original packaging
- Cosmetic Blemishes – Scratches, rub marks or other minor cosmetic imperfections
- Service/Repair – Product has been serviced to the factory original specification
- Factory Returns – Product has been returned in its original condition

Solid State
UV Flood
Light
Systems
(Recertified
05-P)

Recertified products are inspected for damage and any necessary repairs are made. Products are then certified by Edmund Optics® to be in good working order. Since quantity is low, recertified products are sold on a first come, first serve basis. Any imperfections will be listed in the description, indicated in the

A\$3,600.00 1 In Stock

stock number, and categorized by the table below. When purchasing recertified products, the Edmund Optics® standard [return policy](#) applies.

View all our [recertified products](#) in the Web Specials section of our website.

Parts		Cosmetic	
05	All Original Parts Included	P	Perfect
04	Missing Manual	N	Minor Defect/Scratches
03	Missing Manual and Small Accessory	J	Major Defect/Scratches
02	Missing Manual and Large Accessory		



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com