

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Neutral Density \(ND\) Filters](#)

TECHSPEC® VIS-NIR Neutral Density (ND) Filters



- Consistent Transmission from 350 – 1100nm
- Optical Densities from 0.1 to 3.0 Available
- Combine Filters for Custom Optical Densities

Common Specifications

General

Note:

Optical density values are average over specified blocking wavelength range.

Physical & Mechanical Properties

Thickness (mm): 1.00 ±0.20

Clear Aperture (%): 90

Optical Properties

Angle of Incidence (°): 0

Substrate: N-BK7	Coating: Surface 1: Inconel
Surface Quality: 60-40	Blocking Wavelength Range (nm): 350 - 1100
Transmitted Wavefront, P-V: $\lambda/4$ (measure pre-coating)	

Technical Information

Products

Optical Density OD (Average)	Dia. (mm)	Dimensions (mm)	Stock Number	Price	Buy
0.1	12.50	-	#26-482	A\$59.33	20+ In Stock
0.15	12.50	-	#26-483	A\$59.33	20+ In Stock
0.2	12.50	-	#26-484	A\$59.33	20+ In Stock
0.3	12.50	-	#26-485	A\$59.33	20+ In Stock
0.4	12.50	-	#26-486	A\$59.33	20+ In Stock
0.5	12.50	-	#26-487	A\$59.33	3 In Stock
0.6	12.50	-	#26-488	A\$59.33	20+ In Stock
0.7	12.50	-	#26-489	A\$59.33	20+ In Stock
0.9	12.50	-	#26-490	A\$59.33	20+ In Stock
1.0	12.50	-	#26-491	A\$59.33	6 In Stock
1.3	12.50	-	#26-492	A\$59.33	7 In Stock
1.5	12.50	-	#26-493	A\$59.33	20+ In Stock
2.0	12.50	-	#26-495	A\$59.33	20+ In Stock
2.5	12.50	-	#26-496	A\$59.33	14 In Stock
3.0	12.50	-	#26-497	A\$59.33	2 In Stock
0.1	25.00	-	#26-498	A\$85.70	20+ In Stock
0.15	25.00	-	#26-499	A\$85.70	15 In Stock
0.2	25.00	-	#26-500	A\$85.70	5 In Stock
0.3	25.00	-	#26-501	A\$85.70	20+ In Stock
0.4	25.00	-	#26-502	A\$85.70	5 In Stock
0.5	25.00	-	#26-503	A\$85.70	Contact Us
0.6	25.00	-	#26-504	A\$85.70	14 In Stock
0.7	25.00	-	#26-505	A\$85.70	20+ In Stock
0.9	25.00	-	#26-506	A\$85.70	13 In Stock

1.0	25.00	-	#26-507	A\$85.70	14 In Stock
1.3	25.00	-	#26-508	A\$85.70	8 In Stock
1.5	25.00	-	#26-509	A\$85.70	20+ In Stock
2.0	25.00	-	#26-510	A\$85.70	6 In Stock
2.5	25.00	-	#26-511	A\$85.70	16 In Stock
3.0	25.00	-	#26-512	A\$85.70	7 In Stock
0.1	50.00	-	#26-513	A\$121.95	Contact Us
0.15	50.00	-	#26-514	A\$121.95	4 In Stock
0.2	50.00	-	#26-515	A\$121.95	11 In Stock
0.3	50.00	-	#26-516	A\$121.95	20+ In Stock
0.4	50.00	-	#26-517	A\$121.95	10 In Stock
0.5	50.00	-	#26-518	A\$121.95	8 In Stock
0.6	50.00	-	#26-519	A\$121.95	3 In Stock
0.7	50.00	-	#26-520	A\$121.95	20+ In Stock
0.9	50.00	-	#26-521	A\$121.95	13 In Stock
1.0	50.00	-	#26-522	A\$121.95	15 In Stock
1.3	50.00	-	#26-523	A\$121.95	14 In Stock
1.5	50.00	-	#26-524	A\$121.95	Contact Us
2.0	50.00	-	#26-525	A\$121.95	14 In Stock
2.5	50.00	-	#26-526	A\$121.95	15 In Stock
3.0	50.00	-	#26-527	A\$121.95	Contact Us
0.1	-	50.00 x 50.00	#26-528	A\$121.95	5 In Stock
0.15	-	50.00 x 50.00	#26-529	A\$121.95	3 In Stock
0.2	-	50.00 x 50.00	#26-530	A\$121.95	15 In Stock
0.3	-	50.00 x 50.00	#26-531	A\$121.95	20+ In Stock
0.4	-	50.00 x 50.00	#26-532	A\$121.95	1 In Stock

0.5	-	50.00 x 50.00	#26-533	A\$121.95	9 In Stock
0.6	-	50.00 x 50.00	#26-534	A\$121.95	5 In Stock
0.7	-	50.00 x 50.00	#26-535	A\$121.95	14 In Stock
0.9	-	50.00 x 50.00	#26-536	A\$121.95	20+ In Stock
1.0	-	50.00 x 50.00	#26-537	A\$121.95	20+ In Stock
1.3	-	50.00 x 50.00	#26-538	A\$121.95	Contact Us
1.5	-	50.00 x 50.00	#26-539	A\$121.95	14 In Stock
2.0	-	50.00 x 50.00	#26-540	A\$121.95	5 In Stock
2.5	-	50.00 x 50.00	#26-541	A\$121.95	Contact Us
3.0	-	50.00 x 50.00	#26-542	A\$121.95	5 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com