

IDS U3-3861LE-M-GL-VU, USB 3.0, 1/2.8" Monochrome Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye LE/XLE Camera (C/CS - Mount, Full Housing, Front View)



Stock #78-133 [CONTACT US](#)

- 1 + A\$736⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | A\$736.00 each |
| Need More? | Request Quote |

Product Downloads

SPECIFICATIONS

General

Monochrome Camera **Type:**
Model Number:

U3-3861LE-M-GL-VJ

Manufacturer:
IDS Imaging Development Systems

Camera Series:
uEye+ LE

Spectrum:
Monochrome

Physical & Mechanical Properties

Dimensions (mm):
36 x 36 x 26 (excludes connectors and lens mount)

Weight (g):
15

Housing:
Board Level

Sensor

Image Buffer:
Not Specified

Sensor Format:
1/2.8"

Resolution (Megapixels):
2.12

Frame Rate (fps):
135.00

Pixels (H x V):
1,936 x 1,096

Pixel Size, H x V (µm):
2.90 x 2.90

Sensing Area, H x V (mm):
5.61 x 3.175

Imaging Sensor:
Sony IMX290

Type of Sensor:
Progressive Scan CMOS

Shutter Type:
Rolling

Pixel Depth:
12 bit

Exposure Time:
0.011ms - 1649ms

Dynamic Range (dB):
72.00

Machine Vision Standard:
USB3 Vision

Electrical

Power Consumption (W):
1 - 1.5

Hardware & Interface Connectivity

Interface:
USB 3.0

Connector:
USB Type-C

Power Supply:
Power over USB

GPIO Connector Type:
10-pin Wuerth connector (WR-WTB 1.00 mm)

Threading & Mounting

Mount:
S-Mbunt (M12 x 0.5)

Environmental & Durability Factors

Operating Temperature (°C):
0 to +55

Storage Temperature (°C):
-20 to +80

Regulatory Compliance

Certificate of Conformance:
[View](#)

PRODUCT DETAILS

- Up to 8.0MP Resolution with Framerrates up to 230fps
- Board Level Options with C/CS-Mount or S-Mount Available
- GenICam USB3 Vision Compliant

IDS Imaging uEye LE/XLE USB3.1 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GenICam and USB3 Vision standards for ease of software development and integration. These cameras are available in board-level or housed options with S-Mount or C/CS-Mount versions. The C/CS-Mount configurations come with a 5mm spacer to easily adapt between C-Mount and CS-Mount lenses. IDS Imaging uEye LE/XLE USB3.1 Cameras are ideal for small device construction, medical technology, robotics, and machine vision applications. With a compact design, the XLE version is suitable for integration into embedded systems whereas the LE version is suitable for small device projects.
