

FOCAL LENGTH (EFL):  $12,5 \pm 0,13$

BACK FOCAL LENGTH (BFL):  $10,988$

1 AR COATING: NIR I  
 $R(\text{AVG}) \leq 0,5\%$  FROM 600-1050nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$9,81 \pm 0,01$ CX	GLASS N-SF11 785/258	R	$\infty$ PL
Øe	9		Øe	9
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,27'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT  
 SCALE: NONE  
 $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 10,0mm Dia, x 12,5mm FL, NIR I Coated, Plano-Convex Lens

DWG NO 38335

SHEET SIZE A4  
 SHEET 1 OF 1