

## NOTES:

- VIBRATION RATING:
   5 Hz: Vertical = 70-85%, Horizontal = 75-90%
   10 Hz: Vertical = 90-97%, Horizontal = 90-97%
- 2. FEED PRESSURE (psi): 80 (nitrogen or air)
- 3. CONSTRUCTION:

TOP: STAINLESS STEEL CORE: ALL STEEL, HIGH DENSITY, CELL-SIZED HONEYCOMB CORE FRAME: MEDIUM TEXTURE BLACK POWDER COAT

- 4. WEIGHT: 600 lbs
- 5. LOAD CAPACITY (lbs): GROSS: 1400 NET: 350
- 6. ROHS: COMPLIANT





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

THIRD ANGLE PROJECTION		TITLE	900 x 1200mm, LOW PROFILE LAB TABLE	
ALL DIMS IN	mm	DWG NO	33783	SHEET 1 OF 1

