


[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Specialty Mirrors](#)

UV Hot Mirrors



- Transmits 80% of UV and Visible Light
- Reflects 70% of IR Light
- [Contact Us](#) for Custom Sizes

Common Specifications

Physical & Mechanical Properties

Thickness (mm): 3.00 ±0.2

Clear Aperture (%): 90

Optical Properties

Angle of Incidence (°): 0

Coating: Hot Mirror, 0°

Substrate: [Fused Silica](#) (Corning 7980)

Surface Quality: 80-50


Coating Specification: $R_{avg} > 70\% @ 800 - 1050nm$
 $T_{avg} > 80\% @ 245 - 460nm$

Wavelength Range (nm): 245 - 1050


Surface Flatness (P-V): 3 - 5λ

Coating Type: Dielectric

Technical Information



UV Hot Mirrors



Products

AOI (°)	Dia. (mm)	Dimensions (mm)	Thickness (mm)	Stock Number	Price	Buy
0	25.00	-	3.00	#46-587	A\$248.85 Volume Pricing	20+ In Stock
0	-	25.0 x 25.0	3.00	#46-588	A\$248.85 Volume Pricing	7 In Stock
0	50.00	-	3.00	#46-589	A\$380.69 Volume Pricing	13 In Stock
0	-	50.0 x 50.0	3.00	#46-590	A\$380.69 Volume Pricing	20+ In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com