

[All Products](#) / [Testing and Detection](#) / [Amplifiers](#)

Current Amplifier Modules



- Convert Small Currents to Usable Voltages
- Variable Gain
- High Speed and Low Noise Designs

Common Specifications

General

Remote Control:	Yes
-----------------	-----

Physical & Mechanical Properties

Weight (g):	320.00
-------------	--------

Electrical

Input Current Noise (fA/√Hz):	See datasheet
-------------------------------	---------------

Hardware & Interface Connectivity

Power Supply:	Power Supply Required and Sold Separately: USA: #59-180 Europe: #59-180 Japan: Not Available Korea: Not Available China: #59-180
---------------	---

Environmental & Durability Factors

Operating Temperature (°C):	0 to +60
-----------------------------	----------

Technical Information

Products

Transimpedance Gain (Ω)	Input Current Noise (fA/ $\sqrt{\text{Hz}}$)	Bias Voltage	Remote Control	Bandwidth (-3 db)	Stock Number	Price	Buy
$10^3 - 10^{11}$ (adjustable in decade steps)	See datasheet	Adjustable by trimpot	Yes	500KHz max.	#59-178	A\$5,632.00 Volume Pricing	Contact Us
$10^2 - 10^8$ (adjustable in decade steps)	See datasheet	Adjustable by trimpot	Yes	200MHz max.	#59-179	A\$5,632.00 Volume Pricing	5 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com