



FOCAL LENGTH (EFL): 30 ±0,3

BACK FOCAL LENGTH (BFL): 25,12

- 1 UV-AR
 R(ABS) ≤ 1,0% FROM 250 - 425nm @ 0° AOI
 R(AVG) ≤ 0,75% FROM 250 - 425nm @ 0° AOI
 R(AVG) ≤ 0,5% FROM 370 - 420nm @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 25,272 CX			GLASS Fused Silica 458/678 Nd: 1,458	R 25,272 CX		
Øe 29				Øe 29		
λ SEE NOTE 1				λ SEE NOTE 1		
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm		
4/ -				4/ 2,18'		
5/ 40 - 20				5/ 40 - 20		
6/ -			6/ -			
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE 30mm Dia x 30mm FL, UV-AR Coated, Double-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	26600
					SHEET T SIZE	A4
					SHEET 1 OF 1	