

[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [UV and IR Windows](#)

Pure (Undoped) YAG Windows




- Excellent Mid-Wave IR (MWIR) (4 - 5 μ m) Transmission
- Available in 5, 10, 12.5, and 25mm Diameters
- Commonly Used in White Light Generation



Common Specifications

Physical & Mechanical Properties			
Bevel:	Protective as needed	Clear Aperture (%):	90
Thickness (mm):	1.00 ±0.1	Edges:	Fine Ground
Knoop Hardness (kg/mm²):	1,215.00	Parallelism (arcmin):	<3
Poisson's Ratio:	0.28	Young's Modulus (GPa):	300
Optical Properties			
Abbe Number (v _d):	56	Axis Orientation:	<100>
Coating:	Uncoated	Index of Refraction (n _d):	1.81
Substrate:	Yttrium Aluminium Garnet (YAG)	Surface Quality:	40-20
Wavelength Range (nm):	210 - 5500		
Material Properties			
Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):		8.2	
Density (g/cm³):		4.56	

Technical Information



Products

Dia. (mm)	Thickness (mm)	Stock Number	Price	Buy
5.00	1.00	#19-541	A\$299.94 Volume Pricing	20+ In Stock
10.00	1.00	#19-542	A\$342.78 Volume Pricing	20+ In Stock
12.50	1.00	#19-543	A\$428.48 Volume Pricing	1 In Stock
25.00	1.00	#19-545	A\$557.02 Volume Pricing	20+ In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com