

TECHSPEC[®] 10mm FL f/5.6, Blue Series IR-Cut M12 Lens



Stock **#24-456** 2 In Stock

-

1

+

A\$136⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-49	A\$136.00 each
Qty 50+	A\$108.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Blue SeriesSeries:

M12 Imaging Lens	Type:
Yes	IR Cut Filter:
IR-Cut Filter	Special Type of Lens:
Physical & Mechanical Properties	
Fixed	Iris Option:
17.00	Length (mm):
14	Maximum Diameter (mm):
14	Outer Diameter (mm):
5	Weight (g):
Optical Properties	
Horizontal Field of View @ Max Sensor Format: 27.1°	
Field of View at Max Sensor Format: Horizontal: 71.8mm - 27.1° Vertical: 53.8mm - 20.5° Diagonal: 89.9mm - 33.6°	
Horizontal Field of View, 1/3" Sensor: 71.8mm - 27.1°	
Horizontal Field of View, 1/4" Sensor: 53.8mm - 20.5°	
6.00	Maximum Image Circle (mm):
0.0056	Numerical Aperture NA, Object Side:
5(4)	Number of Elements (Groups):
400 - 700	Wavelength Range (nm):
10.00	Focal Length FL (mm):
150 - ∞	Working Distance (mm):
f/5.6	Aperture (f/#):
-0.25 @ Full Field	Distortion (%):
6.6 - 6.3	Back Focal Length BFL (mm):
N/4 MgF ₂ @ 550nm	Coating Specification:
8.45	Entrance Pupil Position (mm):
8.24	Object Space Principal Plane (mm):
-3.29	Image Space Principal Plane (mm):
-0.25	Maximum Distortion (%):
-3.08	Exit Pupil Position (mm):
VS (IR-Cut Filter)	Lens Wavelength Range:
Sensor	
1/3"	Maximum Sensor Format:
1.40	Pixel Size (μm):
Threading & Mounting	
N/A	Filter Thread:
S-Mount (M12 x 0.5)	Mount:

Regulatory Compliance	
Compliant	RoHS 2015:
	View
Compliant	Certificate of Conformance:
	View
Compliant	Reach 247:
	View

PRODUCT DETAILS


- Up to ½", S-Mount Lens
 - Up to 5 MegaPixels, 1.4µm Pixel Size Sensors
 - High Resolution Board Camera Lens Optimized for Close WD
 - 2mm to 35mm Focal Length
 - [Ruggedized Designs](#) Also Available
- TECHSPEC® Blue Series M12 Lenses feature high resolution performance, along with the same great versatility of our [TECHSPEC® Green Series M12 Lenses](#). Each lens consists of several precision glass elements mounted in a compact, aluminum housing. These lenses can connect to C-Mount cameras using the M12 x0.5 Adapter for C-Mount Cameras ([#53-675](#)) or the M12 x0.5 C-Mount Adapter with Rubber O-Ring ([#59-241](#)) for vibration-sensitive environments. TECHSPEC® Blue Series M12 Lenses are ideal for automotive, industrial, and medical imaging application. Prescription data is available by submitting a [Request for Prescription Form](#).
- Note:** Compatible [TECHSPEC® M12 Imaging Lens Accessories](#) available.

Edmund Optics has created multiple product families of our TECHSPEC® M12 S-Mount Lenses, which are designed to provide high resolution. These high performance lenses feature precision glass designs in a metal housing and have optimized specifications between each product family to meet your application needs.

- Blue Series M12 Lenses: High resolution finite conjugate designs optimized for machine vision working distances.
- [Rugged Blue Series M12 Lenses: Stabilized ruggedization](#) versions of our Blue Series M12 Lenses, utilizing the same optics.
- [Green Series M12 Lenses](#): Finite conjugate designs optimized for machine vision working distances.
- [Red Series M12 Lenses](#): Infinite conjugate designs optimized for high resolution performance out to infinity.
- [HEO Series M12 Lenses](#): Harsh Environment Optics (HEO) sealed versions of our Red Series M12 Lenses.
- [Liquid Lens M12 Lenses](#): Integrated liquid lens for fast electronic focus.

TECHNICAL INFORMATION

Focal Length	A	B	C*	D
2.0mm	18.0mm	21.7mm	2.26mm	4.75mm
3.0mm	14.0mm	17.1mm	4.8 - 4.7mm	5.8mm
4.0mm	14.0mm	19.7mm	6.1 - 6.0mm	4.4mm
5.0mm	14.0mm	14.6mm	4.0 - 3.9mm	3.7mm
6.0mm	14.0mm	14.1mm	6.9 - 6.8mm	4.5mm
8.0mm	14.0mm	12.3mm	8.8 - 8.6mm	3.7mm
10.0mm	14.0mm	17.0mm	6.6 - 6.3mm	3.7mm
12.5mm	15.0mm	22.9mm	10.1 - 9.7mm	4.8mm
17.5mm	14.0mm	20.7mm	5.8 - 4.9mm	7.6mm
25.0mm	18.0mm	30.0mm	8.5 - 6.5mm	11.5mm
35.0mm	18.0mm	29.5mm	18.72 - 14.0mm	14.5mm



*Specified for Optimized Working Distance of 150 - 250mm.