

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Ultrafast Laser Mirrors](#)

TECHSPEC®

PeakPower High LDT Low GDD Ultrafast Mirrors



- High Femtosecond Laser Damage Threshold exceeding 0.75J/cm² for 25fs Pulse Duration at 920nm
- > 99.5% Reflectivity with Near Zero Group Delay Dispersion
- [Platinum-Level 2024 Laser Focus World \(LFW\) Innovators Award](#)

Common Specifications

Physical & Mechanical Properties

Edges:	Commercial Polish	Bevel:	Protective as needed
Optical Properties			
Surface Quality:	10-5	Surface Flatness (P-V):	λ/10

Technical Information

Products

Title	Stock Number	Price	Buy
PeakPower Low-GDD Ultrafast Dielectric Mirror, 920nm, 45° AOI, 12.7mm Dia., 6.35mm Thick	#29-520	A\$461.44 Volume Pricing	11 In Stock
PeakPower Low-GDD Ultrafast Dielectric Mirror, 920nm, 45° AOI, 25.4mm Dia., 6.35mm Thick	#29-521	A\$675.68 Volume Pricing	20+ In Stock
PeakPower Low-GDD Ultrafast Dielectric Mirror, 920nm, 45° AOI, 50.8mm Dia., 9.53mm Thick	#29-522	A\$1,178.32 Volume Pricing	4 In Stock
Max PeakPower Low-GDD Ultrafast Dielectric Mirror, 920nm, 45° AOI, 12.7mm Dia., 6.35mm Thick	#29-523	A\$543.84 Volume Pricing	20+ In Stock
Max PeakPower Low-GDD Ultrafast Dielectric Mirror, 920nm, 45° AOI, 25.4mm Dia., 6.35mm Thick	#29-524	A\$758.08 Volume Pricing	20+ In Stock
Max PeakPower Low-GDD Ultrafast Dielectric Mirror, 920nm, 45° AOI, 50.8mm Dia., 9.53mm Thick	#29-525	A\$1,260.72 Volume Pricing	10 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com