

8", IR 940nm, Medium Intensity Linear Backlights

See More by [Advanced Illumination](#)



Advanced Illumination Medium Intensity Linear Backlights

Stock **#18-644** CLEARANCE **1 In Stock**

-

1

+

A\$2,048^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	A\$2,048.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General	
BL31308-940IC	Model Number:
50000	LED Lifetime (hours):
Type of Illumination:	

LED Illuminator	
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available	
Advanced Illumination	Manufacturer:
Backlight	Geometry:
Constant	Illumination Mode:
Physical & Mechanical Properties	
216.4 x 32.2 x 21.7	Dimensions (mm):
263	Weight (g):
204.4 x 25	Active Area (mm):
Optical Properties	
IR	Color:
940.00	Wavelength (nm):
Electrical	
0.8A	Minimum Input Current:
Hardware & Interface Connectivity	
Flying Leads	Connector:
24V	Input Voltage (V):
Power Supply: Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	
Environmental & Durability Factors	
0 - 50	Operating Temperature (°C):
IP50	Environmental Rating:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 233:

PRODUCT DETAILS

- Intense, Diffuse Output up to 226,000 Lux
- Full Range of Wavelengths Available
- UltraSeal Washdown Backlights for Harsh Environments Also Available
- Optional Manual Intensity Adjustments ([#86-887](#) and [#89-555](#)) Recommended

Advanced Illumination Medium Intensity Linear Backlights provide intense, diffuse illumination up to 226,000 Lux. These backlights are available in a full range of wavelengths for seamless system integration. Advanced Illumination Medium Intensity Linear Backlights are ideal for applications such as line scan and object silhouetting. IP69K certified Advanced Illumination UltraSeal Washdown Backlights for harsh environment applications are available.

Note: Requires 24V power supply [#66-855](#). Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are recommended and sold separately.

3D-Printable Mount Files



Bar or Line Light Configuration

**DOWNLOAD
NOW**

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to 1/4-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.



Application Note

Illumination Mounts for Machine Vision Applications
[Read](#) 



Video

Assembly of 3D Printed Mounts for Common Illumination Geometries
[Watch](#) 