

Pixelink®

A NANITAR COMPANY

PL-X9512

CMOS | 10GigE | SONY IMX253 | GLOBAL SHUTTER

The PL-X family of high performance machine vision cameras, with 10 Gigabit ethernet, offers speed, accuracy and reliability in a quick and easy set-up. The 10GBASE-T interface and packet resend capability provide high quality, reliable image transfer at cable lengths of up to 100m on CAT6A. Additional features include Power over Ethernet (PoE), Trigger over Ethernet (ToE) and IEEE1588 clock synchronization (PTP).

The Pixelink PL-X9512 camera features the Sony Pregius IMX253 12MP CMOS sensor which provides low read noise and excellent image quality.



KEY FEATURES

12 MP
CMOS

65
65 fps

3.45 μ m

17.6 mm

SENSOR
SIZE
1.1"

8 & 12-BIT

COLOR

MONO

10GBASE-T

10GiGE®
VISION

TYPICAL APPLICATIONS

- Automated Inspection
- Sports Analysis
- VR and AR Applications
- Multi-camera Synchronization
- Broadcasting
- 3D Mapping
- Research

SENSOR

Sensor	Sony IMX253
Type	CMOS Global Shutter
Resolution	12 MP (4096 x 3000)
Pixel Pitch	3.45µm x 3.45µm
Active Area	17.6 mm diagonal

PERFORMANCE SPECIFICATIONS

FPN	<0.03% of signal
PRNU	<0.7% of signal
Dynamic Range	70 dB
Bit Depth	8 bit and 12 bit
Color Data Formats	Bayer 8, Bayer 12 Packed, Bayer 16, YUV422, RGB 24, BGR 24
Mono Data Formats	Mono 8, Mono 12 Packed & Mono 16

FRAME RATES

Effective Resolution	Free Running
4096 x 3000	Up to 65 fps
* Frame rate will vary based on host system and configuration.	
** Above calculations based on fixed frame rate mode & 8-bit pixel depth.	

INTERFACES

Board Level Trigger Connector	8-pin Molex 1.25 mm pitch
Enclosed Trigger Connector	Hirose M12 (12-pin)
Trigger	Software and hardware
Board Level Trigger Input	1 input, 3.3V (with internal pullup resistor)
Enclosed Trigger Input	1 optically isolated, 5-12V DC at 4-11 mA
Board Level GPO/Strobe	2 outputs, 3.3V
Enclosed GPO/Strobe	1 optically isolated, 5-12V DC at 4-11 mA, 2 outputs, 3.3V
Board Level GPI Input	1 input, 3.3v
Enclosed GPI Input	1 optically isolated, 5-12V DC at 4-11 mA
10GBase-T Connector	M12 X-coded (8-pin)

MECHANICALS

Dimensions (mm)	125 x 57 x 57
Weight (g)	560
Mounting	C-Mount

POWER REQUIREMENTS

Voltage Required	5V (from USB Type-C connector), 48V (802.3bt PoE)
------------------	---

BOARD LEVEL GPIO INTERFACE PIN NAME & DESCRIPTION

1	3.3V power output
2	TRIGGER 3.3V HCMOS input
3	Ground
4	GPO1, 3.3V HCMOS output
5	GPO2, 3.3V HCMOS output
6	Clock, 3.3V (I2C access for OEMs)
7	Data, 3.3V (I2C access for OEMs)
8	GPI, 3.3V HCMOS input
Board connector: Molex (8-pin, 1.25mm pitch, vertical)	
Cable receptacle: Molex 51021-0800;	
Cable crimp terminals: Molex 50079-8100	

ENCLOSED GPIO INTERFACE PIN NAME & DESCRIPTION

1	5.0V output
2	TRIGGER + (optically isolated)
3	TRIGGER- (optically isolated)
4	Data, 3.3V (I2C access for OEMs)
5	GPO1 + (optically isolated)
6	GPO1- (optically isolated)
7	GPO1, 3.3V HCMOS output
8	GPO2, 3.3V HCMOS output
9	Ground
10	GPI+ (optically isolated)
11	GPI- (optically isolated)
12	Clock, 3.3V (I2C access for OEMs)

ENVIRONMENTAL & REGULATORY

Compliance	FCC, CE & RoHS
Operating Temperature	0°C to 50°C
Storage Temperature	-45°C to 85°C


SOFTWARE

Pixelink Capture	Control & operate multi-camera
Pixelink SDK	Software Development Kit


COMPUTER & OPERATING SYSTEM (minimum requirements)

Processor	Intel Core i5 ARMv7 (32-bit) or (ARMv8 (64-bit) recommended)
Memory	8GB RAM (16 GB multi-channel DDR4 recommended)
Hard Drive	200MB (SSD recommended)
BUS	PCIe 3.0 with a slot supporting x8 transfers
Operating System	Windows 7/8/10 (Windows 10 recommended) Ubuntu 16.04/18.04/20.04

RESPONSIVITY CURVE - COLOR



RESPONSIVITY CURVE - MONO



PIXELINK CAPTURE

Pixelink Capture is powerful multi-camera software application designed to configure “n” number of cameras and stream “n” number of cameras simultaneously in real-time high-quality video viewed in a multi-window environment. It offers options for complex image enhancements such as exposure control and filtering, in addition to multi-camera application testing and configuration.

Pixelink Capture features allow you to measure supporting point, line, circle, rectangle, polyline and polygon measurements while determining pixel location. The user can review and adjust data before exporting the findings to an Excel spreadsheet for further analysis.

Pixelink Capture also has integrated lens control (zoom & focus) for Navitar motorized lenses and accurate autofocus options for Navitar motorized fine focus mechanisms.

LINKS FOR MECHANICAL DRAWINGS

- [Enclosed Mechanical Drawing](#)
- [Board Level Configuration](#)
- [Board Level Configuration with Flex Cable](#)

PIXELINK SDK

Providing full control of all camera functions, the Pixelink Software Development Kit (SDK) is the software package of choice for developers and system integrators who are integrating Pixelink cameras into their applications. The Pixelink SDK provides access to the full Pixelink Application Programming Interface (API) and provides sample applications, wrappers for many 3rd party controls, such as LabVIEW, along with full documentation.

The Pixelink SDK is compatible with Microsoft Windows and popular Linux platforms. When using the Pixelink SDK, developers can integrate Pixelink cameras into their applications with ease.

AVAILABLE CONFIGURATIONS

- PL-X9512CG-BL
- PL-X9512MG-BL
- PL-X9512CG-T
- PL-X9512MG-T

COLOR SPACE

- C = Color
- M = Mono
- NIR = Near Infrared

INTERFACE

G = 10 GigE

HOUSING

- BL = Board Level
- T = Trigger