


TECHSPEC® PeakPower High LDT Low GDD Ultrafast Mirrors


Coating Specification:
Rs > 99.50% @ 840 - 1010nm @ 45° AOI
Rp > 99.50% @ 870 - 960nm @ 45° AOI
Theoretical Reflection Curve



© COPYRIGHT 2020 EDMUND OPTICS, INC. ALL RIGHTS RESERVED

TECHSPEC® PeakPower High LDT Low GDD Ultrafast Mirrors

GDD Specification:
GDDs $0 \pm 50 \text{ fs}^2$ @ 840 - 1010nm @ 45° AOI
GDDp $0 \pm 50 \text{ fs}^2$ @ 880 - 960nm @ 45° AOI
Theoretical GDD Curve



© COPYRIGHT 2020 EDMUND OPTICS, INC. ALL RIGHTS RESERVED