






- NOTES:
- 1. SUBSTRATE:  
N-BK7
  - 2. COATING (APPLY ACROSS CLEAR APERTURE)  
  
S1 & S2: VIS 0° (425-675nm)  
R(avg) ≤0.4% @ 425 - 675nm
  - 3. FINE GROUND SURFACE
  - 4. POWER, IRREGULARITY, AND SURFACE QUALITY  
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
  - 5. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	50.00	 <b>Edmund Optics®</b>		
SHAPE	CONVEX	PLANO	BFL	46.04			
RADIUS	25.84	∞			TITLE	30mm H x 30mm L x 50mm FL VIS 0° Coated, Illumination Grade PCX Cylinder Lens	
SURFACE QUALITY	60 - 40	60 - 40					
CLEAR APERTURE	29.00 x 29.00	29.00 x 29.00	ALL DIMS IN	mm	DWG NO	25502	SHEET 13 OF 16
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					