

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Aspheric Lenses](#) / [Glass Molded](#)

Rochester Precision Optics (RPO) Visible Molded Glass Aspheric Lenses



- Precision Visible Glass Molded Lenses
- Ideal for High Volume Production Requirements
- Multiple Glass Substrates Available

Common Specifications

Physical & Mechanical Properties

Bevel:	Protective as needed
---------------	----------------------

Optical Properties

Aspheric Design Wavelength (nm):	633
---	-----

Coating:	BBAR (400 - 600nm)
-----------------	--------------------

Coating Specification:	$R_{avg} < 1\%$ @ 400 - 600nm
-------------------------------	-------------------------------

Surface Quality:	60-40
-------------------------	-------

Wavelength Range (nm):	400 - 600
-------------------------------	-----------

Technical Information

Products

Dia. (mm)	CT (mm)	EFL (mm)	NA	Substrate	CA (mm)	Stock Number	Price	Buy
#73-654 New								
								
New								
Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!								
7.20	5.00	11.00	0.26	D-K59	5.50		A\$140.08	20+ In Stock
#73-658 New								
								
New								
Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!								
7.33	2.93	5.30	0.55	H-ZLaF52	5.83		A\$206.00	7 In Stock

[#73-661 New](#)



New

Launched
on our
website
before
appearing
in our
latest print
catalogs.
Be the
first to buy
before
anyone
else!

4.40 3.06 2.59 0.60 H-ZLaF50B 3.12

A\$206.00

20+ In Stock

[#73-665 New](#)



New

Launched
on our
website
before
appearing
in our
latest print
catalogs.
Be the
first to buy
before
anyone
else!

6.33 3.19 3.10 0.62 H-ZLaF52 5.40

A\$140.08

20+ In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com